

Product Index

A

AC Adapters	1098, 1949, 2002, 2010, 2027-2041
Adapters	
Bluetooth	8, 14, 20, 50, 1210
D-Sub	1220, 1261, 1269
I/O	20, 1087, 1195, 1220
Modular	1195, 1204, 2116
Phono (RCA)	1083, 1085, 1133, 1168, 1170
RF	14, 1082, 1085, 1132, 1145, 1147, 1149, 1151, 1153-1154, 1156, 1159, 1161-1163, 1165, 1167-1168, 1170-1171, 1173-1174, 1176, 1178-1179, 1181-1182
SMT	14, 2160
Socket	207, 1151, 1480-1481
XLR	1133, 1137
Alarms	603, 1064, 1811-1813, 2014, 2169
Alligator Clips	2109-2111
Alternistors	(See Semiconductors)
Amplifiers	(See Semiconductors)
Analog ICs	(See Semiconductors)
Antennas	5-6, 9, 11, 19, 21, 23, 938, 943, 1003, 1230, 1874
Arrays	
Capacitor	617, 754
Resistor	612, 615-616, 618-619
Attenuators	1182, 1684
Audible Signal Devices	
Alarms	1811-1813
Benders	1814
Buzzers	1806-1807, 1809-1813
Earphones	1803
Electret Condenser Microphone	1803, 1809, 1816
Elements	
Microphone	1803
Piezo	1814
Hardware	1812
Indicators	
Electromagnetic	1813
Electromechanical	1815
Piezo	1813
Piezo	1812-1814
Ringers	1807, 1812
Sirens	1813, 1818
Sonalerts	1811-1813
Speakers	1804-1805, 1808, 1812, 1817-1818
Transducers	1805, 1812, 1814, 1818
Automotive	
12VDC Jacks and Plugs	1084
Connectors	1084, 1408, 1471, 1487
LED	(See Illumination)
Relays	1717-1721, 1771-1772

B

Basic Stamp	43-44
Batteries	
1/2AA	2061-2062, 2066
1/3AA	2057
2/3AA	2057, 2063, 2066
2/3AA	2057, 2061-2062
4/5A	2057
AAAA	2056
A	2057, 2063, 2066
AA	2055-2058, 2062, 2065-2066
AAA	2055-2058, 2065
C	2055-2058, 2062-2063
D	2055-2058, 2062
F	2057
N	2055-2057
SC	2057-2058
9V	2055-2057, 2061, 2066
Alkaline	2055-2056, 2065
Battery Packs	2057-2058, 2061-2062
Button Cell	2061, 2065
Calculator	2065
Camera	2065
Carbon Zinc	2055-2056, 2065
Chargers	
Lead Acid	2059
Lithium Polymer	2066
Nickel-Metal Hydride	2057
Coin Cell	2061, 2063-2065
Computer	2065
Electronic	2065, 2087
Hearing Aid	2065
Lantern	2055-2056
Lead Acid	2055, 2059-2060
Lithium	426, 2055, 2061-2066
Manganese Dioxide	2065
Memory Backup	2061-2062
Nickel-Cadmium	2055, 2057-2058
Nickel-Metal Hydride	2055, 2057-2058, 2061
Photo	2056, 2065
Pure Lead	2060
Rechargeable	2055, 2057-2061, 2063, 2066
Scooter	2055, 2059-2060
Silver-Oxide	2065
UPS	2017, 2047, 2055, 2059-2060
Watch	2065
Wheelchair	2055, 2059-2060
Zinc Chloride	2055-2056
Battery Accessories	
Analyzer	2060, 2084
Chargers	389, 413, 2057, 2059, 2066
Clips	2071, 2073, 2109-2110
Holders	1899, 1910, 2064, 2067-2071, 2073
Indicator Labels	2073
Snaps	1495, 2071-2072
Spring Contacts	2067, 2071, 2073, 2108

Binding Post	1133, 1140-1142, 1182, 2113
Blowers	1879, 1881, 1920, 1927, 1929
Bluetooth	8, 14, 20, 44, 50, 354, 943, 1210
Boxes	(See Enclosures)
Braid	2141, 2145, 2157
Breadboards	216, 2157-2164
Buzzers	1806-1807, 1809-1813

C

Cabinets	
Accessories	1877-1884
Hardware	
Casters	1879, 1881
Leveler	1879
Screws	1879, 1882
Shelves	1880
Slide Bracket	1882
Portable	1884-1885
Racks	1877, 1880, 1883
Utility	1884
Cable	(See Wire and Cable)
Cable Assemblies	(See Wire and Cable)
Cable Ties	1009-1013, 1016-1019, 1024
Capacitors	
Aluminum Electrolytic	
5mm	744
7mm	729, 735, 745
Axial	730, 736, 739-740, 742-743, 746
Bi-Polar	712, 735, 743
Computer Grade	723, 725
Double Layer	726-728
Flatpack	722
General Purpose 85°C	707-709, 712-713, 718, 720, 722-725, 729, 731, 735-736, 738-741, 745-746
High Capacitance	713, 717, 720-727, 735-736, 741
High Frequency	727, 743
High Reliability	730, 733-743
High Ripple	711, 721-722, 725, 730, 733, 743
High Temperature	707-711, 713-716, 719, 721, 724, 727, 729-730, 732-734, 738-739, 742, 745
High Voltage	720-725, 731-732, 736, 739-742, 746
Kit	746
Lead Free	711, 713-716, 731-735
Low ESR	707, 714, 716-717, 722, 730, 743
Low Impedance	708, 711, 729, 733-734
Low Leakage	725, 739, 744
Memory Backup	726-728
Miniature	717, 735, 738-740, 744-746
Mounting Hardware	723
Non-Polar	743, 745
Organic	714, 717
Polymer	714-717
Radial	716-717, 726-727, 729, 731-735, 738, 741-746
Screw Terminal	722-723, 725
Snap Mount	718-721, 724
Supercapacitors	726-728
Surface Mount	707-717, 726, 728
Ceramic	
Arrays	754
Axial	805, 807, 833, 879
Broadband Blocks	766
Chip	747, 751, 753, 755-757, 759-765, 767-791, 795-803
Conformal Coated	804-805, 807-810
Coupling	812, 816
Disc	812-813, 816-819
EMI Suppression	754-755
Fail-Safe	748-749
Floating-Electrode	748-749
Flexible Termination	747-753
Flexicap	750-752
Flexiterm	747, 749-751
General Purpose	770-776, 783-788, 795-798
Half-Turn	878
High Capacitance	752, 754-755, 762, 768, 779-784, 786-790, 795-796, 804, 806-814, 816-819
High Q	752-753, 755, 758-760, 762-765
High Temperature	768-776, 783-790, 794, 803-804, 806-812, 814
High Voltage	747, 752-753, 759-761, 765, 769, 789-790, 792-794, 799, 806-808, 810, 812-813, 816-819
Interdigitated	755
Kits	751, 762, 765-766, 768-769
Lead Free	875
Low ESL / Low ESR	755, 760, 777-778, 786-788
Molded	806-807, 812
Multilayer	747-750, 752, 754-765, 767-776, 779-791, 795-799, 801-806, 809-810, 812, 814, 879
Multi-Turn Trimmer	875-879
Open-Mode	749, 751-753
Radial	804-819, 833, 879
RF Microwave	758-759, 766
Surface Mount	747-803
Tin/Lead Termination	761, 767
Tip and Ring	757, 769, 792
Trimmer	875-879
Feedthru (Arrays & Capacitors)	754-755
Film	
Axial	825, 833-835, 841-842
Chip	821
DC Link	828-829
Dipped	840
Film/Foil	835, 838-839
Kits	823, 842
Metalized	
Box	831, 834, 841
Paper	832
Polycarbonate	835
Polyester	820-827, 831-838, 841

Polyphenylene	832
Polypropylene	822, 825-826, 831-839, 842
Multilayer	823
Non-Inductive	841
Orange Drop	836
Polyester	820-827, 831-838, 840-841
Polypropylene	822, 825-826, 828-839, 842
Polystyrene	842
Radial	820-824, 826-828, 831-834, 836-842
Snubbers	826, 830, 839
Suppression	826-827, 831-833
Surface Mount	820-821
Switching	828-829
High Reliability	730, 733-734
Mica	843-845
Mounting Hardware	723
Silicon Chip	846
Supercapacitors	726-728
Surface Mount	617, 651, 707-717, 726, 728, 747-803, 820-821, 844, 846-855, 846, 857-866, 875-876, 878, 929, 1487
Tantalum	
Axial	870, 872, 874
Dipped	867-869, 871
Fail-Safe Fused	861
Hermetically Sealed	870
High Temperature	849, 852, 854-855, 857, 861, 873
Lead Free	847, 850-851, 854-855, 865
Low ESR	847-849, 852-855, 859-865, 870
Low Profile	862-863
Niobium Oxide	847
Polymer	851, 854-855
Radial	867-869, 871
Surface Mount	847-855, 857-866
Wet	873-874
Trimmer	875-879
Card Readers	327, 1320-1321, 1327-1328, 1332, 1431
Cases	917, 935, 1884, 1888-1890, 1892, 1895-1897, 1903, 1910, 1915, 2082-2084, 2088-2089, 2091
CCFLs	119
Chassis	1878, 1881, 1884, 1889, 1895
Chemicals	
Adhesives	1030, 2142, 2144
Anti-Static Coating	2144
Bottles	2137, 2156
Circuit Board Repair Pens	2142, 2145
Cleaners	2137, 2141-2142, 2144-2145, 2150-2151, 2155-2156
Conformal Coating	2144, 2156
Dispensers	1009, 2137, 2142, 2152, 2156
Dusting Gas	2142, 2155
Flux	2139-2142, 2155
Freezers	2142
Heat Sink Compound	1939, 2144, 2156
Leadcheck Tester	2142
Lubricant	1009, 2135, 2142, 2145, 2156-2157
Pumps	2156
Threadlocker	2157
Transistor Grease	2144
Wipes	2142, 2144-2145, 2155
Chip Coolers	1920
Chokes/Coils	(See Inductors)
Circuit Board Indicators	(See Illumination)
Circuit Breakers	
Hydraulic/Magnetic	1796-1797, 1800
Push-to-Reset	1799-1800, 1802
Seals	1677
Thermal	1112, 1797-1802
Thermo Magnetic	1793-1794, 1798
Circuit Protection	
Circuit Breakers	1796-1802
DIN Rail	576, 1541, 1796, 1798, 1802, 2018, 2048, 2050
Filters	448, 545, 551-552, 2018, 2048
Fuse Blocks	599-602, 610-611, 1541
Fuse Clips	599-602, 611
Fuse Holders	594, 599-602, 610-611, 1541
Fuses	583, 585, 587-598, 603-609, 1541
Gas Discharge Tubes	569, 576-579, 586
Metal Oxide Varistors	567, 571-575
ESD Devices	