

# TOSHIBA Diodes

**TOSHIBA**  
Leading Innovation >>>

## TOSHIBA ZENER DIODES

RoHS Compliant This product is RoHS compliant.



RoHS Compliant

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Reverse Voltage	Power Dissipation	Price Each			
					1	100	250	1000
757-015AZ3.3-XTH3,FT	015AZ3.3-X(TH3,F,T)	ESC-2	3.3V	150mW	.06	.043	.039	.035
757-02D218-X(TPH3,F)	02DZ18-X(TPH3,F)	USC-2	18V	150mW	.06	.043	.039	.035
757-02DZ3.3-X(TPH3,F)	02DZ3.3-X(TPH3,F)	USC-2	3.3V	150mW	.06	.043	.039	.035
757-CRZ10(TE85L,Q)	CRZ10(TE85L,Q)	S-FLAT-2	10V	0.7 W	.38	.26	.23	.21
757-CRZ15(TE85L,Q)	CRZ15(TE85L,Q)	S-FLAT-2	15V	0.7W	.38	.26	.23	.21
757-CRZ16(TE85L,Q)	CRZ16(TE85L,Q)	S-FLAT-2	16V	0.7 W	.33	.23	.20	.18
757-CRZ30(TE85L,Q)	CRZ30(TE85L,Q)	S-FLAT-2	30V	0.7 W	.38	.26	.23	.21

## TOSHIBA SCHOTTKY BARRIER DIODES



RoHS Compliant

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Voltage Output	Current (mA)	Price Each			
					1	10	100	250
757-1SS184T5LFT	1SS184T5LFT	SC-59	80V	100mA	.08	.06	.051	.047
757-1SS193T5LFT	1SS193T5LFT	SC-59	80V	100mA	.08	.06	.051	.047
757-1SS226T5LFT	1SS226T5LFT	SC-59	80V	100mA	.08	.06	.051	.047
757-1SS424(TL3,F,T)	1SS424(TL3,F,T)	ESC-2	20V	200mA	.09	.07	.06	.055
757-1SS388(TL3,F,T)	1SS388(TL3,F,T)	ESC-2	40V	100mA	.09	.07	.06	.055
757-1SS389(TL3,F,T)	1SS389(TL3,F,T)	ESC-2	10V	100mA	.09	.07	.06	.055
757-1SS405(TPH3,F)	1SS405(TPH3,F)	ESC-2	20V	50mA	.09	.07	.06	.055
757-1SS413(TL3,T)	1SS413(TL3,T)	fSC-2	20V	50mA	.09	.07	.06	.055
757-1SS416(TL3,T)	1SS416(TL3,T)	fSC-2	30V	100mA	.09	.07	.06	.055
757-1SS416CT(TPL3)	1SS416CT(TPL3)	US6	30V	100mA	.14	.11	.094	.086
757-1SS417(TL3,T)	1SS417(TL3,T)	fSC-2	40V	100mA	.09	.07	.06	.055
757-1SS420(TPL3,F)	1SS420(TPL3,F)	ESC-2	30V	200mA	.09	.07	.06	.055
757-1SS421(TL3,F,T)	1SS421(TL3,F,T)	ESC-2	30V	200mA	.09	.07	.06	.055
757-1SS423(TE85L,F)	1SS423(TE85L,F)	SSM-3	40V	100mA	.28	.22	.19	.17
757-CMS01(TE12L,Q)	CMS01(TE12L,Q)	M-FLAT-2	30V	3A	.52	.42	.36	.31
757-CMS02(TE12L,Q)	CMS02(TE12L,Q)	M-FLAT-2	30V	3A	.57	.46	.39	.34
757-CMS08(TE12L,Q)	CMS08(TE12L,Q)	M-FLAT-2	30V	1A	.31	.25	.21	.19
757-CRS01(TE85L,Q,M)	CRS01(TE85L,Q,M)	S-FLAT-2	30V	1A	.27	.22	.188	.171
757-CRS02(TE85L,Q)	CRS02(TE85L,Q)	S-FLAT-2	30V	1A	.26	.21	.18	.16
757-CRS02(TE85L,Q,M)	CRS02(TE85L,Q,M)	S-FLAT-2	30V	1A	.26	.21	.18	.16
757-CRS03(TE85L,Q)	CRS03(TE85L,Q)	S-FLAT-2	30V	1A	.20	.156	.133	.121
757-CRS03(TE85L,Q,M)	CRS03(TE85L,Q,M)	S-FLAT-2	30V	1A	.20	.156	.133	.121
757-CRS04(TE85L,Q,M)	CRS04(TE85L,Q,M)	S-FLAT-2	40V	1A	.33	.25	.195	.174
757-CRS06(TE85L,Q,M)	CRS06(TE85L,Q,M)	S-FLAT-2	20V	1A	.28	.228	.194	.177
757-CRS08TE85LQM	CRS08(TE85L,Q,M)	S-FLAT-2	30V	1.5A	.25	.21	.17	.15
757-CRS09(TE85L,Q,M)	CRS09(TE85L,Q,M)	S-FLAT-2	30V	1.5A	.26	.21	.18	.16

## TOSHIBA SWITCHING DIODES



RoHS Compliant

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Voltage Output	Average Current	Price Each			
					1	10	100	250
757-1SS352(TH3,F,T)	1SS352(TH3,F,T)	USC-2	80V	100	.05	.036	.031	.028
757-1SS387CT(TPL3)	1SS387CT(TPL3)	ESC-2	80V	100	.09	.07	.06	.055
757-1SS387TH3FT	1SS387TH3FT	ESC-2	80V	100	.07	.054	.046	.042
757-1SS403(TPH3,F)	1SS403(TPH3,F)	USC-2	200V	100	.07	.054	.046	.042
757-1SS426(TPL3,F)	1SS426(TPL3,F)	UF6-2	80V	100	.07	.06	.06	.055
757-1SS427(TPL3)	1SS427(TPL3)	UF6-2	80V	100	.09	.07	.06	.055

## TOSHIBA SWITCHING DIODES



RoHS Compliant

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Voltage Output	Average Current	Price Each			
					1	10	100	250
757-CRH01(TE85L,Q)	CRH01(TE85L,Q)	S-FLAT-2	200V	1A	.28	.22	.19	.17

## TOSHIBA VERICAP DIODES



RoHS Compliant

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Voltage (V)	Capacitance (pF)	Price Each			
					1	10	100	250
757-1SV229TPH3F	1SV229TPH3F	USC-2	15V	14 to 16	.20	.16	.136	.124
757-1SV239TPH3F	1SV239TPH3F	USC-2	15V	3.8 to 4.7	.23	.18	.153	.14
757-1SV270TPH3F	1SV270TPH3F	USC-2	10V	15 to 17	.20	.16	.136	.124
757-1SV276TPH3F	1SV276TPH3F	USC-2	10V	15 to 17	.20	.16	.136	.124
757-1SV277TPH3F	1SV277TPH3F	USC-2	10V	4.0 to 4.9	.20	.16	.136	.124
757-1SV279TH3FT	1SV279TH3FT	ESC-2	15V	14 to 16	.25	.20	.17	.155
757-1SV280TH3FT	1SV280TH3FT	ESC-2	15V	3.8 to 4.7	.20	.16	.136	.124
757-1SV281TH3FT	1SV281TH3FT	ESC-2	10V	15 to 17	.20	.16	.136	.124
757-1SV284(TH3,F,T)	1SV284(TH3,F,T)	ESC-2	10V	15 to 17	.14	.114	.096	.088
757-1SV285TH3FT	1SV285TH3FT	ESC-2	10V	4.0 to 4.9	.20	.16	.136	.124
757-1SV311TH3FT	1SV311TH3FT	ESC-2	10V	9.7 to 11.1	.21	.17	.145	.132
757-1SV314TH3FT	1SV314TH3FT	ESC-2	10V	7.3 to 8.4	.25	.20	.17	.155
757-1SV304TPH3F	1SV304TPH3F	USC-2	10V	17.3 to 19.3	.21	.17	.145	.132
757-1SV305TH3FT	1SV305TH3FT	ESC-2	10V	17.3 to 19.3	.21	.17	.145	.132
757-1SV310TPH3F	1SV310TPH3F	USC-2	10V	9.7 to 11.1	.21	.17	.145	.132