



Dimensions in mm
and (In.)

Features:

- 3 Way: 671-0300, 164-7103
- 5 Way 45°: 164-7150
- 5 Way 60°: 164-7151
- 5 Way dice: 164-7152
- 6 Way: 164-7106
- 7 Way: 164-7107
- 8 Way: 164-7180

- Current: 4 Amps
- Rating: 34V d.c. 24V a.c.
- Contact Resistance: 10 milli-ohms
- Insulation Resistance: 10³ mega-ohms
- Working Temperature +70°C to -20°C
- Material: Noryl SE 100-701