



Dimensions mm (In.)

Part Number	Wire Length (L1)	
	mm	In.
121-2614	102 ± 5	4 ± .2
121-2615	127 ± 5	5 ± .2
121-2616	152 ± 5	6 ± .2
121-2618	203 ± 10	8 ± .4
121-2611	254 ± 10	10 ± .4
121-2612	305 ± 10	12 ± .4

Specifications:

- Wire: non UL 26AWG
- Insulation: red, black PVC
- Red (+) black (-)