



Dimensions (In.)

Specifications:

- Tolerance: ±3%
- Leads: 22AWG

Mouser Stock No.	L (μH) ±3%	Q Min.	Test Freq. (kHz)	Min. S.R.F. (MHz)	D.C.R. Max. (Ω)	Max. DC Current (mA)	Coil Form
43HG337	0.33	45	25.0	360	0.09	1400	Phenolic
43HG397	0.39	45	25.0	310	0.12	1225	Phenolic
43HG687	.068	45	25.0	310	0.12	1225	Phenolic
43HG106	1.0	50	25.0	200	0.29	785	Phenolic
43HG226	2.2	33	7.9	135	0.95	435	Phenolic
43HG276	2.7	33	7.9	120	1.20	385	Phenolic
43HG336	3.3	33	7.9	110	2.00	300	Phenolic
43HG476	4.7	33	7.9	90	2.60	260	Phenolic
43HG105	10	55	7.9	45	0.90	290	Ferrite
43HG155	15	65	2.5	40	1.40	240	Ferrite
43HG225	22	75	2.5	30	2.50	175	Ferrite
43HG335	33	65	2.5	19	3.00	165	Ferrite
43HG395	39	60	2.5	14.5	2.60	176	Ferrite
43HG475	47	55	2.5	13	2.75	170	Ferrite
43HG685	68	55	2.5	11	3.30	156	Ferrite
43HG104	100	50	2.5	9.5	4.50	133	Ferrite
43HG154	150	65	.79	8	6.05	114	Ferrite
43HG224	220	65	.79	6.2	7.45	103	Ferrite
43HG474	470	65	.79	3.9	17.9	100	Ferrite
43HG103	1000	55	.79	2.3	33.1	74	Ferrite