

Models 7162, 7163 AND 7164
1/4" Phone Jack/Jack and Plug/Plug Adapters*Model 7162 1/4" Phone Jack Adapter-2 Cond (Mono)**Model 7163 1/4" Phone Jack Adapter-3 Cond (Stereo)**Model 7164 1/4" Phone Plug Adapter-2 Cond (Mono)*

Use Pomona couplers and adapters to connect standard commercial phone jacks and plugs.

Features

- Mono and stereo versions
- Low contact resistance
- Easy installation

Materials

- Body is nickel-plated (gold-7164) diecast zinc alloy.
- Contacts are nickel-plated brass (gold plated brass-7164).

Ordering Information

Model: 7162, 7163, 7164

Specifications

Number of contacts	2 (Mono), 3 (Stereo)
Contact resistance	$\leq 3 \text{ m}\Omega$
Dielectric strength	1000 V dc

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.