


THIS DOCUMENT IS THE PROPERTY OF KEYSTONE ELECTRONICS CORP. AND SHALL NOT BE REPRODUCED, DISTRIBUTED OR USED AS A BASIS FOR MANUFACTURE WITHOUT PRIOR WRITTEN PERMISSION FROM KEYSTONE ELECTRONICS CORP.



P/N	TH'D	COLOR
4198	10-32	WHITE
4199	10-32	YELLOW

6	1	HEAD	NYLON	-
5	2	WASHER, INSULATOR	NYLON	-
4	2	WASHER, INSERT	BRASS	NICKEL PL.
3	1	WASHER, SPLIT	BRASS	NICKEL PL.
2	2	NUT	BRASS	NICKEL PL.
1	1	SHAFT 10-32 TH'D	BRASS	NICKEL PL.
NO.	QTY	DESCRIPTION	MAT'L	FINISH

### KEYSTONE ELECTRONICS CORP.

ASTORIA, N.Y. 11105-2017

PART NAME

STANDARD 'HEX' BINDING POST

MATERIAL

AS NOTED

FINISH

AS NOTED

DRN BY

BOONE

DATE

4.19.04

APP'D

LN

SCALE

X

2.17.06 CHANGE AS PER ECN 06-013

A

TOLERANCES INCH [MM]  
 DECIMAL  $\pm .005$  [ $\pm 0.15$ ]  
 ANGULAR  $\pm 1^\circ$   
 UNLESS OTHERWISE SPECIFIED

CODE

C/M

DWG NO.

4198-4199

DATE

DESCRIPTION

REV.