



FEP Flat Ribbon Cable

I.D.C.

Product Description

FEP (Fluorinated Ethylene Propylene) insulated conductors extruded in ribbon format for ease of termination with standard I.D.C.'s (Insulation Displacement Connectors).

Features & Benefits

- Extruded - Will Not Delaminate
- Tight Pitch Tolerances
- High Temp (200° C)
- Resistant to Chemicals
- Environmentally Stable
- High Performance Dielectric Insulation
- Non-combustible

Product Scope

| Center Spacing | .050" | .025" | .0394" (1 mm) |
|----------------|--|---|-------------------|
| Conductor | 26 AWG, 7/34, SPC 26 AWG, 7/34 Bare 28 AWG, 7/36, SPC 28 AWG, 7/36 Bare | 30 AWG, Solid, SPC 32 AWG, 7/40, SPC | 28 AWG, 7/36, SPC |
| Signal Count | 10 to 64 | 10 to 100 | 10 to 80 |

* For termination with standard I.D.C.'s

Specialty: Custom Constructions