



TOLERANCE FOR "L" LENGTH

DIMENSION RANGE	TOLERANCE
0.0m - 1.0m	+10/0 mm
>1.0m - 3.0m	+30/0 mm
>3.0m - 5.0m	+50/0 mm
>5.0m - 10.0m	+100/0 mm
>10.0m	+200/0 mm

NOTES:

- 1) CABLE MUST BE PERFORMED 100% CONTINUITY TEST.
- 2) WHITE LABEL CONTENT:

CMK/YR-XXXXX-X-XX
HARTING P/N

BLACK FONT, FONT HEIGHT: 3.5.

- 3) CABLE SHOULD BE FOLDED MANY CIRCLES ACCORDING TO TOTAL CABLE LENGTH AND PACKED BY A PLASTIC BAG (QTY ACCORDING TO ACTUAL CONDITION),STICK THE LABEL WITH P/N,QTY AND LOT NUMBER ON IT,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION).
- 4) THE CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY CONTENT.

33 18 243 100 0067	1 m
33 18 243 080 0066	0.8 m
33 18 243 050 0065	0.5 m
33 18 243 020 0064	0.2 m
33 18 243 010 0063	0.1 m

Part-No. Dim.L

Tech Character.				Free size tolerances	
All tolerances in mm	Def.	How	Scale	Def.	How
Original Size DIN A 3	Def.	As per	/	Def.	As per
	Top				
	Stand				

Mod.	Doc.	Name	ZHANG HARTING LIMITED	Scale	TB 33 18 243 xxx 00xx	Page	/
------	------	------	-----------------------	-------	-----------------------	------	---

A 1 2 3 4 5 6 7 8

A 1 2 3 4 5 6 7 8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33182430100063](#) [33182430200064](#) [33182430500065](#) [33182430800066](#) [33182431000067](#)