

60 Watt Universal Input
.....
PSA-65U Single Output Series



Features

- Compact Low Profile Case
- Non-vented/Spill-proof Case
- Class B EMI Compliant
- IEC320 C14 Grounded Input

Applications

- Notebook Computers
- Peripherals
- Portable Equipment
- Networking

Safety Approvals

- UL 1950
- TUV EN60950
- CSA 22.2 950 (cUL)

Mechanical Characteristics

- Dimensions:
- Length: 150.5mm (5.9in)
 - Height: 39mm (1.5in)
 - Width: 70.5mm (2.8in)
 - Weight: 550gm (20oz)

Output Specifications

Model	DC Output Voltage	Load		Ripple(1) P-P(max)	Regulation Line & Load
		Min.	Max.		
PSA-65U-120	12V	0.1A	5A	120mV	±5%
PSA-65U-150	15V	0.1A	4A	150mV	±5%
PSA-65U-180	18V	0.1A	3.3A	180mV	±5%
PSA-65U-240	24V	0.1A	2.5A	240mV	±5%

(1) Measured at full load by using a 12in. twisted pair terminated with a 10mfd capacitor and a 0.1mfd ceramic in parallel.

NONSTOP

