



|             |                |                 |                  |                       |                            |
|-------------|----------------|-----------------|------------------|-----------------------|----------------------------|
| PART NUMBER | ITEM ①<br>DB25 | ITEM ②<br>CABLE | ITEM ③<br>DB25   | ITEM ④<br>SCREW       | ITEM ⑤<br>CONTACT          |
| SEE TABLE I | MALEMO<br>LDED | NOTE 1          | FEMALEM<br>OLDED | 4-40 THREAD<br>MOLDED | GOLD PLATED<br>2-3 MICRONS |

|                                       |                  |   |   |   |                                   |
|---------------------------------------|------------------|---|---|---|-----------------------------------|
| DRAWING NO.<br>30-9506MF(SEE TABLE I) |                  |   |   |   |                                   |
| REVISIONS                             |                  |   |   |   |                                   |
| 01                                    | OFFICIAL RELEASE |   |   |   | 2009.09                           |
|                                       | 08-05-09         | Y | Y | T | 08<br>Betty<br>09:08:16<br>+08'00 |



**受控 CONTROLLED DOCUMENT**

|           |           |           |    |                  |           |
|-----------|-----------|-----------|----|------------------|-----------|
| 编号<br>P/N | 30-95XXMF | 版本<br>Rev | 01 | 日期<br>Rel'd Date | SEP 14,09 |
|-----------|-----------|-----------|----|------------------|-----------|



- NOTES:**
- CABLE: 25 CONDUCTORS,PVC JACKET CABLE,28 AWG,DRAIN WIRE, FOIL SHIELD, NON-UL TYPE, BEIGE COLOR JACKET.
  - ELECTRICAL SPECIFICATIONS  
CURRENT RATING: 5 AMPS  
INSULATOR RESISTANCE: 100KOHMS
  - PRODUCT SHOULD BE RoHS COMPLIANCE.
  - PACKAGING REQUIREMENT FOLLOWS ENGINEER DOCUMENT P/N 836-40200001XX

**TABLE I**

| PART NUMBER | DESCRIPTION                   | LENGTH (FEET) | TOLERANCE (INCHES) |
|-------------|-------------------------------|---------------|--------------------|
| 30-9506MF   | D-25M TO D-25 FM 25 COND.6FT  | 6             | ±1.00              |
| 30-9510MF   | D-25M TO D-25 FM 25 COND,10FT | 10            | ±1.00              |
| 30-9525MF   | D-25M TO D-25 FM 25 COND,25FT | 25            | ±2.00              |

THIS DRAWING TO BE INTERPRETED PER ANSI Y 14.5M - 1994

**COMPANY CONFIDENTIAL**

|                                                                                 |                        |                  |                                           |
|---------------------------------------------------------------------------------|------------------------|------------------|-------------------------------------------|
| TOLERANCE UNLESS OTHERWISE SPECIFIED                                            | DRAWN BY<br>BETTY.YU   | DATE<br>08-05-09 | <br><b>Connectivity Solutions</b>         |
| DECIMALS                                                                        | CHECKED BY<br>BETTY.YU | DATE<br>08-05-09 |                                           |
| X ± 0.2                                                                         | APPROVED BY<br>THOMAS  | DATE<br>08-05-09 |                                           |
| X.XX ± 0.1                                                                      |                        |                  |                                           |
| ANGLES ± 0.5°                                                                   | U/M                    | mm               |                                           |
| THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY. |                        |                  | SHEET<br>1 OF 1                           |
|                                                                                 |                        |                  | DRAWING NO.<br>30-9506MF<br>(SEE TABLE I) |
|                                                                                 |                        |                  | SIZE<br>C                                 |