

Color-Keyed®

TBM14M



Self-contained hydraulic tool with colour-coded interchangeable dies. Swivelled C-shaped head rotates 180°. Complete with carrying case. Incorporates the Shure-Stake™ mechanism.

T&B Catalog Number: **TBM14M**
EAN Number: 05414363111054
UPC Number: 78621078971
Description: Hand tool (hydraulic tool) for Color-Keyed® copper tube lugs and splices

Technical Information

Tooling Functionality	Crimping
Type	Hand tool
Version	hydraulic tool
Ordering Information	
Terminal Brand	Color-Keyed®
Terminal Type	Power cable connectors
Terminal	copper tube lugs and splices
Die Product Ref.	15520, 15522, 15527CK, 15508, 15513CK, 15508, 15526, 15530, 15511, 15510CK, 15534, 15514CK, 15512, 15506, 15611, 15505, 15515CK, 15603
Die Type	interchangeable (delivered separately)
Crimping range (mm ²)	6 - 450 (8 AWG - 1000 kcmil)
Crimping Mechanism	Shure-Stake™ mechanism ensures a complete crimp cycle before the tool releases
Output Force (ton)	14
Weight (g)	6800