

- Length (mm [in]) = 38.50 [1.515]
- Mechanical - Width Class = 30mm to 40mm Class
- Width (mm [in]) = 35.50 [1.398]
- Mechanical - Height Class = 40mm to 50mm Class
- Height (mm [in]) = 48.50 [1.909]
- Insulation - Clearance Between Contact and Coil (mm [in]) = 4 [0.157]
- Insulation - Creepage Between Contact and Coil (mm [in]) = 14.9 [0.587]

- Other:**
- Series = RM8
 - Brand = Schrack
 - Additional Features = Mechanical Indicator, Manual Operation

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[AODA Accessibility Policy](#)
[AODA Multi-Year Accessibility Plan](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

