



[Home](#) > [Products](#) > [By Type](#) > [Relays](#) > [Product Feature Selector](#) > Product Details

KM-17 Product Details



KM-17
(3-1618162-6)

TE Internal Number: 3-1618162-6

[Active](#)

High Voltage Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- Contact Arrangement = 1 Form B, SPST-NC, 1 N/C, 1 Form A, SPST-NO, 1 N/O, 1 Form C, SPDT, 1 C/O, 2 Form C, DPDT, 2 C/O
- Power Switching = Make Only, No
- Contact Current Rating = 0 - 10 Amps.
- Not RF Rated
- Coil Voltage = 12 VDC

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none">• None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none">• None Available <p>Product Specifications:</p> <ul style="list-style-type: none">• None Available <p>Application Specifications:</p> <ul style="list-style-type: none">• None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none">• None Available <p>CAD Files:</p> <ul style="list-style-type: none">• None Available	<p>Additional Information:</p> <ul style="list-style-type: none">• Product Line Information <p>Related Products:</p> <ul style="list-style-type: none">• Tooling
Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none">• Termination Style = Coil Leads <p>Electrical Characteristics:</p> <ul style="list-style-type: none">• Contact Current Rating (Amps.) = 0 - 10• RF Rated = No• Coil Voltage (VDC) = 12• Voltage, Max. (VDC) = 0 - 7500• Current, Carry Only = Yes <p>Termination Related Features:</p> <ul style="list-style-type: none">• High Voltage Connection (Power) = Flying Leads• High Voltage Connection (Coil) = Coil Leads• Auxiliary Contacts = Without	<p>Body Related Features:</p> <ul style="list-style-type: none">• Mount Style = Threaded <p>Configuration Related Features:</p> <ul style="list-style-type: none">• Contact Arrangement = 1 Form B, SPST-NC, 1 N/C, 1 Form A, SPST-NO, 1 N/O, 1 Form C, SPDT, 1 C/O, 2 Form C, DPDT, 2 C/O• Power Switching = Make Only, No• High Voltage Connection Length (mm [in]) = 304.8 [12]• Economizer = Without <p>Industry Standards:</p> <ul style="list-style-type: none">• RoHS/ELV Compliance = Not ELV/RoHS compliant• Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C <p>Other:</p> <ul style="list-style-type: none">• Brand = Kilovac

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)