



# Photographic Tape

## 235

### Technical Data

**Product Description** 3M™ Photographic Tape 235 is a black colored opaque paper tape used in general purpose camera applications.

Product Construction	Backing	Adhesive	Color	Standard Roll Length
	Crepe paper	Black pigmented rubber	Black	60 yds. (55 m)

### Typical Physical Properties

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

		ASTM Test Method
Adhesion to Steel:	23 oz./in. width (25 N/100 mm)	D-3330
Tensile Strength at Break:	22 lbs./in. width (386 N/100 mm)	D-3759
Elongation at Break:	9%	D-3759
Backing Thickness:	5 mils (0.12 mm)	D-3652
Total Tape Thickness:	7 mils (0.17 mm)	D-3652

### Features

- Not recommended for outdoor applications.
- Firm adhesive for clean removal except from kraft paper.
- Low gloss backing that reduces light reflection.
- Crepe backing which is conformable for photo can sealing.

### Application Ideas

- Masking out unwanted portions of negatives.
- Repairing camera bellows.
- Sealing film envelopes and metal film containers.

# 3M™ Photographic Tape

235

---

**Storage** Store under normal conditions of 70°F (21°C) and 50% R.H. in the original carton.

---

**Shelf Life** To obtain best performance, use this product within 12 months from date of manufacture.

---

**Product Use** All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

---

**Warranty and Limited Remedy** Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

---

**Limitation of Liability** Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

**ISO 9001:2000**

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



**Industrial Business  
Industrial Adhesives and Tapes Division**

3M Center, Building 21-1W-10, 900 Bush Avenue  
St. Paul, MN 55144-1000  
800-362-3550 • 877-369-2923 (fax)  
www.3M.com/industrial



*Recycled Paper  
40% pre-consumer  
10% post-consumer*

Printed in U.S.A.  
©3M 70-0703-2467-1 (1999/5/05)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)

[235-3/4"x60yd](#) [235-1"x60yd](#) [235-2"x60yd](#)