

Safety runs in the family.



Your hands are everything. Protect them with the technology and craftsmanship you can trust. For decades, 3M has been a leader in innovative personal safety for the body, head, ears, eyes and now, hands.

3M™ Comfort Grip Gloves - General Use

The Lightweight Heavyweight

Nitrile palm coating makes these gloves a light, flexible, abrasion-resistant and long lasting alternative to many cotton and latex palm-coated gloves. They provide excellent grip, even in wet or oily conditions.



The nylon stretch liner gives you a breathable, “second skin” fit and makes these gloves ideal for light- to medium-duty jobs that require precision handling, especially in hot and sweaty conditions.


Typical Applications

- General material handling
- Handling small parts
- Electrical component assembly
- Carpentry, plumbing, roofing

3M™ Comfort Grip Gloves - Cut Resistant

A Cut Above

These medium-duty gloves have the same features and comfort as the 3M General Use Gloves with even greater cut, puncture and tear resistance. They're excellent for jobs requiring dexterity when handling sharp parts.



Two varieties allow you to customize your cut level to the job's requirements. ANSI Cut Level A3, EN388 TDM Cut Level D glove is nitrile foam coated, while the ANSI Cut Level A1, EN388 TDM Cut Level B glove is polyurethane coated.

Typical Applications

- Handling abrasive or sharp materials
- Forming, bending or machining sharp parts
- Cable pulling and wire handling
- Cable preparation

Strong grip. Exceptional dexterity. Long lasting.

3M™ Comfort Grip Gloves - Winter



The Cold Weather Hotshot

These new 3M winter grade gloves have the comfort and dexterity of our 3M General Use Gloves but with added warmth for cold weather applications. They are nitrile foam coated for better grip.

Typical Applications

- General material handling
- Handling small parts
- Electrical component assembly
- Carpentry, plumbing, roofing
- Irrigation

The difference is in the grip.

These hardworking gloves are washable and feature a knit wrist cuff style.



3M Style	UPC	Size	MOQ (pair/bag)	ANSI Level*	EN388 Level**
3M™ Comfort Grip Gloves - General Use					
CGM-GU	00-54007-98954-7	8M	6	N/A	3122A
CGL-GU	00-54007-98955-4	9L	6		
CGXL-GU	00-54007-98956-1	10XL	6		
3M™ Comfort Grip Gloves - Cut Resistant (ANSI Cut Level A3, EN388 TDM Cut Level D)					
CGM-CR	00-54007-98957-8	8M	6	A3	4444D
CGL-CR	00-54007-98958-5	9L	6		
CGXL-CR	00-54007-98959-2	10XL	6		
3M™ Comfort Grip Gloves - Cut Resistant (ANSI Cut Level A1, EN388 TDM Cut Level B)					
CGM-CRE	00-51128-61032-9	8M	6	A1	4342B
CGL-CRE	00-51128-61033-6	9L	6		
CGXL-CRE	00-51128-61034-3	10XL	6		
3M™ Comfort Grip Gloves - Winter					
CGM-W	00-54007-99150-2	8M	6	N/A	2121A
CGL-W	00-54007-99151-9	9L	6		
CGXL-W	00-54007-99152-6	10XL	6		

*ANSI 105-2016 Cut Level (A1 – A9). Previous ANSI ratings based on ANSI 105-2011 Cut Level (0-5). For more information on ratings changes, please reach out to your 3M sales representative

**EN 388:2016: Abrasion Level (1-4), Coupe Cut Level (1-5), Tear (1-4), Puncture (1-4), TDM Cut Test (A-F). Please note that the TDM cut resistance test is the reference performance result, and the Coupe test results are only indicative where both cut resistance test results are shown for EN388:2016. Previous EN 388 levels based on EN 388 2003: Abrasion (1-4), Coupe cut test (1-5), Tear (1-4), Puncture (1-4). For more information on ratings changes, please reach out to your 3M sales representative



3M Electrical Markets Division
 3M Austin Business Center
 13011 McCallen Pass, Bldg. C
 Austin, Texas 78753
 Phone 800 245 3573
 Fax 800 245 0329
 Web www.3M.com/electrical

Important Notice. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability. 3M's product warranty is stated in its Product Literature available upon request. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any direct, indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.

© 3M 2019. All rights reserved. 3M is a trademark of 3M Company. (Janz)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)

[CGXL-CR](#) [CGM-CR](#) [CGXL-GU](#) [CGL-GU](#) [CGL-CR](#) [CGM-GU](#) [CB-1000](#)