



Technical Data

3M™ Enzyme Digester

Description

3M™ Enzyme Digester controls odors by eliminating their source.

Use and Features

- Safe for use on most carpet styles and fibers
- A stable, non-pathogenic bacteria capable of digesting fats, oils, grease, protein, starch, and other organic waste
- Follow precautions and use directions on the label

Applications

- For use on carpet, drains, sewers, traps, and upholstery

Packaging

- 32-ounce bottle (quart)
- 12 bottles per case
- Ready-to-Use only

General Use Directions

Drains and Pipes

1. Pour directly into drain on lowest floor of building; using 2 oz. per inch of pipe diameter (e.g., use 4 oz. for a 2" pipe).

Pipe Size	2"	4"	6"	8"
Dosage (2 times per week)	4 oz.	8 oz.	12 oz.	16 oz.

2. For multiple floors, apply product on lowest floor first, then move up one floor per application.
3. For ongoing odor control, apply product 2-4 times per week, depending on drain usage. For multiple floors, apply to the top floor drains 2-4 times per week, and lower drains as needed.

Carpets

1. Apply directly onto odor-causing area.
2. Blot with clean, white cloth. Reapply as needed.

Restrooms

1. Spray bowl or urinal surfaces as needed to eliminate odors.

Grease Traps

1. Pour product daily into sink or pipeline close to the trap. Use 5 oz. for every 20 ft. in trap capacity.

Trap Capacity	Less than 20'	More than 20'
Daily Dose	4-5 oz.	8-10 oz.

2. Pour a cup of warm water to flush product down.

Special Use Directions

- Product should be applied at night or when pipes or traps are used the least to allow culture to grow
- Avoid contact with disinfectants
- Contact with products with a pH <6 or >11 may reduce effectiveness

NOTE:

Refer to product Material Safety Data Sheet for specific physical properties, health hazard, first aid and precautionary information.

3M™ Enzyme Digester MSDS doc. No.

- 21-3550-7

3M Branch Sales Offices

ANCHORAGE

11151 Calaska Circle
Anchorage, AK 99515

Telephone: 907/522-5200
Facsimile 907/522-1645

HONOLULU

4443 Malaai Street
Honolulu, HI 96818
Mail to: P.O. Box 30048
Honolulu, HI 96820

Telephone: 808/422-2721
Facsimile 808/422-9557

CONTINENTAL UNITED STATES

Customer Service Department
3M Center Building 223-5S-07
St. Paul, MN 55144-1000

Order Entry 1-800-852-9722
Facsimile 1-800-447-0408

CANADA

1840 Oxford Street East
London, Ontario, Canada
N5V 3G2
Mail to: P.O. Box 5757
London, Ontario, Canada
N6A 4T1

Telephone: 800/364-3577
Facsimile: 800/479-4453

Important Notice to User

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty and Limited Remedy: 3M warrants that each 3M product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.



Building and Commercial Services Division

St. Paul, MN 55144-1000
1-800-852-9722
www.3M.com/building

3M is a trademark of 3M Company. Used under license in Canada.

© 3M 2012. All rights reserved.

DMR 781166

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)

[7010384734](#)