

3M™ Mini D Ribbon (MDR) Cable Assembly

.050" High Speed Digital Data Transmission System, 100 Pos. 141A0-SZ5B-XXX-0DC



- 24 shielded quad pairs (96 cond.) plus 4 drains
- Solution for high speed datacom and telecom applications
- Each differential pair is shielded with foil and braid for additional signal protection
- Rugged MDR ribbon type contact
- Quick release latches
- RoHS* compliant

Date Modified: October 11, 2005

TS-0966-05
Sheet 1 of 3

Physical

Connector Contact Plating

Wiping Area: 30 μ " [0.76 μ m] Min. Gold

Shell

Plating: Nickel

Material: Aluminum

Cable

Color: Parchment/Beige

Jacket Material: Polyvinyl Chloride (PVC)

Flammability: AWM VW-1

Electrical

Voltage Rating: 30 V

Insulation Resistance: $> 1 \times 10^8 \Omega$ at 100 Vdc

Withstanding Voltage: 350 Vrms for 1 minute

Current Rating: 1 A

Individually Shielded Balanced Quads

Characteristic Impedance: $100 \pm 10 \Omega$

Conductor Size: 30 AWG

Propagation Velocity: 1.45 ns/ft [4.8 ns/m]

Environmental



Temperature Rating: -20°C to +75°C

"RoHS compliant" means that the product or part does not contain any of the following substances in excess of the following maximum concentration values in any homogeneous material, unless the substance is in an application that is exempt under RoHS: (a) 0.1% (by weight) for lead, mercury, hexavalent chromium, polybrominated biphenyls or polybrominated diphenyl ethers; or (b) 0.01% (by weight) for cadmium. Unless otherwise stated by 3M in writing, this information represents 3M's knowledge and belief based upon information provided by third party suppliers to 3M.

UL File No.: E86982

3M™ Mini D Ribbon (MDR) Cable Assembly

.050" High Speed Digital Data Transmission System, 100 Pos. 141A0-SZ5B-XXX-0DC



mm
[Inch]

Tolerance Unless Noted		
	0.0	0.00
mm	±.1	±.10

[] Dimensions for Reference only



Ordering Information

141A0-SZ5B-XXX-0DC

Length: _____
300 = 3 meters
500 = 5 meters

TS-0966-05
Sheet 2 of 3

3M™ Mini D Ribbon (MDR) Cable Assembly

.050" High Speed Digital Data Transmission System, 100 Pos. 141A0-SZ5B-XXX-0DC

MDR 100 Position Pinout F100-1					
Quad	Signal	Pin #	Quad	Signal	Pin #
	LVDS GRND 1	1	2	25M	26
11	1M	51	2	26M	76
11	2M	2	2	25P	27
11	1P	52	2	26P	77
11	2P	3	7	27M	28
12	3M	53	7	28M	78
12	4M	4	7	27P	29
12	3P	54	7	28P	79
12	4P	5	8	29M	30
13	5M	55	8	30M	80
13	6M	6	8	29P	31
13	5P	56	8	30P	81
13	6P	7		LVDS GRND 3	32
14	7M	57	9	31M	82
14	8M	8	9	32M	33
14	7P	58	9	31P	83
14	8P	9	9	32P	34
15	9M	59	10	33M	84
15	10M	10	10	34M	35
15	9P	60	10	33P	85
15	10P	11	10	34P	36
16	11M	61	18	35M	86
16	12M	12	18	36M	37
16	11P	62	18	35P	87
16	12P	13	18	36P	38
17	13M	63	19	37M	88
17	14M	14	19	38M	39
17	13P	64	19	37P	89
17	14P	15	19	38P	40
	LVDS GRND 2	65	20	39M	90
3	15M	16	20	40M	41
3	16M	66	20	39P	91
3	15P	17	20	40P	42
3	16P	67	21	41M	92
4	17M	18	21	42M	43
4	18M	68	21	41P	93
4	17P	19	21	42P	44
4	18P	69	22	43M	94
5	19M	20	22	44M	45
5	20M	70	22	43P	95
5	19P	21	22	44P	46
5	20P	71	23	45M	96
6	21M	22	23	46M	47
6	22M	72	23	45P	97
6	21P	23	23	46P	48
6	22P	73	24	47M	98
1	23M	24	24	48M	49
1	24M	74	24	47P	99
1	23P	25	24	48P	50
1	24P	75		LVDS GRND 4	100

TS-0966-05
Sheet 3 of 3

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

3M

Electronics

6801 River Place Blvd.
Austin, TX 78726-9000
800/328-1368
www.3M.com/electronics

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Minimum 10%
Post-Consumer Fiber

Printed in USA.

© 3M 2005

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[141A0-SZ5B-300-0DC](#) [141A0-SZ5B-500-0DC](#)