

SOLUTIONS PRODUCTS DESIGN SUPPORT BUY & SAMPLE ABOUT CYPRESS

Home > Products > Microcontroller (MCU) and Programmable System-on-Chip (PSoC®) Families > 32-bit Arm® Cortex® Microcontroller (MCU) Families > FM3 32-bit Arm® Cortex®-M3 Microcontroller (MCU) Families > FM3 CY9Ax10A-Series Low Power Arm® Cortex®-M3 Microcontroller (MCU) Family > CY9AF112MAPMC-GNE2

CY9AF112MAPMC-GNE2



Status: **In Production**

Product Specs		Pricing & Inventory		Packaging/Ordering		Quality and RoHS		Technical Documents	
CY9AF112MAPMC-GNE2						DESIGN SUPPORT			
Automotive Qualified		N						Development Kits	
Max. Operating Temp. (°C)		70						Forums	
Max. Operating Voltage (V)		5.50						Knowledge Base	
Min. Operating Temp. (°C)		0						Packaging	
Min. Operating Voltage (V)		1.10						Product Brochures	
Part Family		FM3						Quality & Reliability	
Part Family		FM3						Samples	
Tape & Reel		N						Technical Support	
						Technical Training			
						Third Party Network (CYPros)			
PRICING & INVENTORY AVAILABILITY									
1-9 unit Price*	10-24 unit Price*	25-99 unit Price*	100-249 unit Price*	250-999 unit Price*	1000+ unit Price*				
\$7.40	\$6.66	\$6.07	\$5.48	\$5.03	\$4.00				
Availability	Quantity	Ships In		Buy from Cypress	Buy from Distributors				
Out of Stock	0	Please click here to check lead times		Contact Sales	Contact Sales				
* Prices are shown in United States dollars and are for budgetary use only for volume of 1ku									
PACKAGING/ORDERING									
No. of Pins		80							
Package Cross Section Drawing		Download							
Package Carrier		TRAY							
Package Carrier Drawing / Orientation		Package Orientation							
Minimum Order Quantity (MOQ)		119							
Order Increment		119							
Estimated Lead Time (days)		203							
HTS Code		8542.31.0001							
ECCN Suball		3A991.A.3							
QUALITY AND ROHS									
Moisture Sensitivity Level (MSL)									
Peak Reflow Temp. (°C)		260 (Cypress Reflow Profile)							
RoHS Compliant		Y							
PB Free		Y							
Lead/Ball Finish		Pure Sn							
Marking		Cypress Marking Format							
TECHNICAL DOCUMENTS									
Application Notes (17)									
AN204432 - FM3, FM4 Trace with µVision and ULINK Pro Mar 10, 2021									
AN202487 - Differences Among FM0+, FM3, and FM4 32-Bit Microcontrollers May 29, 2020									
AN205294 - FM3, CY9AF310 Series, TouchScreen_IR Solution Principle Jul 31, 2018									
AN204410 - FM3 Microcontroller Low Voltage Detect Interrupt Circuit Setting/Usage Jul 04, 2018									
Show More ▾									

TRAINING

- Workshops
- Training On-Demand
- Webinars

Automotive
Industrial
Consumer

Wireless
Microcontrollers (MCUs)
Memory
Universal Serial Bus (USB)
Power Management
Touch Sensing
Clocks & Buffers

Community
Videos
Quality & Reliability
Product Roadmaps

Investors
Careers

CORPORATE HEADQUARTERS

Cypress Semiconductor Corp.
198 Champion Court
San Jose, CA 95134 USA
Tel: +1-408-943-2600

CUSTOMER SERVICE SUPPORT

+1-800-541-4736
Hours:
8:00AM - 5:00PM (local time)
Create a MyCase
Cypress Developer Community

INTERNATIONAL SUPPORT

+1-408-943-2600
United States +1-800-541-4736
Hours:
4:30AM - 1:30PM (pacific time)
7:30PM - 4:30AM (standard
time)

OTHER REQUESTS

Contact Us
Report a Website Problem
Report a Security Vulnerability

[ABOUT US](#) [CAREERS](#) [INVESTORS](#) [LEGAL](#)



© Cypress Semiconductor Corporation. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cypress Semiconductor:](#)

[CY9AF112MAPMC-GNE2](#)