


NON-INSULATED SPADE TERMINALS


MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14
AMP.	9	12	17	18	30

TERMINAL MATERIAL: COPPER

WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION ^{inch} mm							CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	d2		W	F	L	E	D	d1	T		
22-16 A.W.G. 0.5-1.5 mm ²	SNB1-3.2 *	SN1-3.2	#4	.126 3.2	.224 5.7	.256 6.5	.630 16.0	.189 4.8	.134 3.4	.067 1.7	.030 0.75	IZUMI MODEL 5N18 WITH DIE INDEX NO.:1.25 OR K.S. MODEL KST2000D-1322 WITH DIE INDEX NO.:22-18 OR K.S. MODEL KM-70L WITH DIE SET NO.:DIE-1322 WITH DIE INDEX NO.:22-18	1000
	SNBS1-3.7 *	SNS1-3.7	#6	.146 3.7									1000
	SNBL1-3.7 *	SNL1-3.7	#6	.146 3.7	.252 6.4								1000
	SNBLL1-3.7	SNLL1-3.7	#6	.146 3.7	.283 7.2								1000
	SNBS1-4 *	SNS1-4	#8	.169 4.3	.252 6.4								1000
	SNBM1-4 *	SNM1-4	#8	.169 4.3	.283 7.2								1000
	SNBL1-4 *	SNL1-4	#8	.169 4.3	.319 8.1								1000
	SNBS1-5 *	SNS1-5	#10	.209 5.3									1000
	SNBL1-5 *	SNL1-5	#10	.209 5.3	.374 9.5								1000
	SNBS1-6 *	SNS1-6	1/4	.252 6.4									1000
	SNBL1-6 *	SNL1-6	1/4	.252 6.4	.472 12.0	.433 11.0	.866 22.0						1000
	SNB1-8	SN1-8	5/16	.331 8.4	.551 14.0	.394 10.0	.831 21.1						1000
16-14 A.W.G. 1.5-2.5 mm ²	SNB2-3.2 *	SN2-3.2	#4	.126 3.2	.224 5.7	.256 6.5	.630 16.0	.189 4.8	.161 4.1	.091 2.3	.031 0.8	IZUMI MODEL 5N18 WITH DIE INDEX NO.:2 OR K.S. MODEL KST2000D-1322 WITH DIE INDEX NO.:16-14 OR K.S. MODEL KM-70L WITH DIE SET NO.:DIE-1322 WITH DIE INDEX NO.:16-14	1000
	SNBS2-3.7 *	SNS2-3.7	#6	.146 3.7									1000
	SNBL2-3.7 *	SNL2-3.7	#6	.146 3.7	.236 6.0								1000
	SNBLL2-3.7	SNLL2-3.7	#6	.146 3.7	.283 7.2								1000
	SNBS2-4 *	SNS2-4	#8	.169 4.3	.252 6.4								1000
	SNBM2-4 *	SNM2-4	#8	.169 4.3	.283 7.2								1000
	SNBL2-4 *	SNL2-4	#8	.169 4.3	.319 8.1								1000
	SNBS2-5 *	SNS2-5	#10	.209 5.3									1000
	SNBL2-5 *	SNL2-5	#10	.209 5.3	.366 9.3								1000
	SNBS2-6 *	SNS2-6	1/4	.252 6.4									1000
	SNBL2-6 *	SNL2-6	1/4	.252 6.4	.472 12.0	.433 11.0	.866 22.0						1000
	SNB2-8	SN2-8	3/8	.331 8.4	.551 14.0	.394 10.0	.823 20.9						1000
	SNB2-10	SN2-10	5/16	.413 10.5	.689 17.5	.512 13.0	.996 25.3						1000



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KS Terminals:](#)

[SNL1-3.7](#)