

HEAT SHRINKABLE-CHANGING DOWN BUTT SPLICE CONNECTORS "HT"(TUBULAR TYPE)

MAXIMUM ELECTRIC CURRENT:

A.W.G.	26	24	22	20	18	16	14	12	10	8
AMP.	5.5	7	9	12	17	18	30	35	50	70


MAXIMUM ELECTRICAL RATING: 600 VOLTS MAX.

SHRINK TEMP.: 150°C OPERATING TEMP.: -40°C~+105°C

INSULATION MATERIAL: HIGH DENSITY PE.

TERMINAL MATERIAL: COPPER TUBULAR

※ NOTE: INSULATION COLOR WITH CHANGING DOWN END COLOR RING.



WIRE RANGE A.W.G. mm ²	ITEM NO.	DIMENSION inch/mm			INSULATION COLOR WITH CHANGING DOWN END COLOR RING	CRIMPING TOOL	Q'TY BOX
		d1	d2	L			
16-14 to 22-16 1.5-2.5 to 0.5-1.5	BHT2CD1	.091 2.3	.087 1.7	1.417 36.0	BLUE WITH RED COLOR RING	K.S. MODEL KST2000G WITH DIE INDEX NO:2	500
12-10 to 16-14 4-6 to 1.5-2.5	BHT5CD2	.134 3.4	.091 2.3	1.614 41.0	YELLOW WITH BLUE COLOR RING	K.S. MODEL KST2000G WITH DIE INDEX NO:5	500
8 to 16-14 8 to 1.5-2.5	BHT8CD2	.181 4.6	.091 2.3	1.909 48.5	RED WITH BLUE COLOR RING	K.S. MODEL KST2000G WITH DIE INDEX NO:8	400
8 to 12-10 8 to 4-6	BHT8CD5	.181 4.6	.138 3.5	1.909 48.5	RED WITH YELLOW COLOR RING	K.S. MODEL KST2000G WITH DIE INDEX NO:8	400

cUL_{us} ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KS Terminals:](#)

[BHT2CD1](#) [BHT5CD2](#)