


DIN 46234

NON-INSULATED RING TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	6	4	2	1/0
AMP.	95	125	170	230

TERMINAL MATERIAL: COPPER


WIRE RANGE A.W.G. mm ²	ITEM NO.	STUD SIZE		DIMENSION mm						CRIMPING TOOL	Q'TY BOX
		d2		d3	I	a	C	d1	S		
6 A.W.G. 16 mm ²	DRNB4-16	#8	4.3	11.0	20.0	10.0	10.5	5.8	1.2	IZUMI MODEL 9H-60 WITH DIE INDEX NO:14 OR KLAUKE MODEL PK25 WITH DIE INDEX NO.:HQ25/16 OR K.S. MODEL LY-2045E OR KSTP-325T WITH DIE INDEX NO:16	500
	DRNB5-16	#10	5.3								500
	DRNB6-16	1/4	6.5	11.0	20.0						500
	DRNB8-16	5/16	8.4	14.0	22.0						500
	DRNB10-16	3/8	10.5	18.0	24.0						500
	DRNB12-16	1/2	13.0	22.0	26.0						400
4 A.W.G. 25 mm ²	DRNB5-25	#10	5.3	12.0	25.0	11.0	12.0	7.5	1.5	IZUMI MODEL 9H-60 WITH DIE INDEX NO:22 OR KLAUKE MODEL PK25 WITH DIE INDEX NO.:HQ25/25 OR K.S. MODEL KSTP-325T WITH DIE INDEX NO:25	250
	DRNB6-25	1/4	6.5	12.0	25.0						250
	DRNB8-25	5/16	8.4	16.0	25.0						250
	DRNB10-25	3/8	10.5	18.0	26.0						200
	DRNB12-25	1/2	13.0	22.0	31.0						200
	DRNB16-25	5/8	17.0	28.0	35.0						200
2 A.W.G. 35 mm ²	DRNB6-35	1/4	6.5	15.0	26.0	12.0	15.0	9.0	1.6	IZUMI MODEL 9H-60 WITH DIE INDEX NO:38 OR KLAUKE MODEL PK25 WITH DIE INDEX NO.:HQ25/35 OR K.S. MODEL KSTP-325T WITH DIE INDEX NO:35	250
	DRNB8-35	5/16	8.4	16.0	26.0						200
	DRNB10-35	3/8	10.5	18.0	27.0						200
	DRNB11-35	7/16	11.5	22.0	31.0						200
	DRNB12-35	1/2	13.0	22.0	31.0						200
	DRNB16-35	5/8	17.0	28.0	36.0						100
1/0 A.W.G. 50 mm ²	DRNB6-50	1/4	6.5	18.0	34.0	16.0	17.0	11.0	1.8	IZUMI MODEL 9H-60 WITH DIE INDEX NO:60 OR KLAUKE MODEL PK25 WITH DIE INDEX NO.:HQ25/50 OR K.S. MODEL KH-150 OR KSTP-325T WITH DIE INDEX NO:50	100
	DRNB8-50	5/16	8.4	18.0	34.0						100
	DRNB10-50	3/8	10.5	18.0	34.0						100
	DRNB12-50	1/2	13.0	22.0	36.0						100
	DRNB16-50	5/8	17.0	28.0	40.0						100

UL cUL ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[DRNB10-16](#) [DRNB10-25](#) [DRNB10-35](#) [DRNB10-50](#) [DRNB12-16](#) [DRNB12-25](#) [DRNB12-35](#) [DRNB12-50](#) [DRNB16-](#)
[25](#) [DRNB16-35](#) [DRNB16-50](#) [DRNB5-16](#) [DRNB5-25](#) [DRNB6-16](#) [DRNB6-25](#) [DRNB6-35](#) [DRNB6-50](#) [DRNB8-16](#)
[DRNB8-25](#) [DRNB8-35](#) [DRNB8-50](#)