


VINYL-INSULATED RING TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	14	12
AMP.	30	35

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.
INSULATION MATERIAL: VINYL
INSULATION COLOR:

14-12 A.W.G.: BLACK

TERMINAL MATERIAL: COPPER


WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION ^{inch} ^{mm}							CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	d2		W	F	L	E	D	d1	T		
14-12 A.W.G. 2.5-4 mm ²	RVBS3-3.2	RVS3-3.2	#4	.126 3.2	.217 5.5		.937 23.8					IZUMI MODEL 214 WITH DIE INDEX COLOR:BLACK OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:BLACK	1000
	RVB3-3.2	RV3-3.2	#4	.126 3.2	.315 8.0		.984 25.0						1000
	RVBS3-4	RVS3-4	#8	.169 4.3	.283 7.2	.315 8.0	.969 24.6						1000
	RVB3-4	RV3-4	#8	.169 4.3	.315 8.0		.984 25.0						1000
	RVBS3-5	RVS3-5	#10	.209 5.3									1000
	RVBM3-5	RVM3-5	#10	.209 5.3	.374 9.5	.362 9.2	1.063 27.0	.512 13.0	.248 6.3	.118 3.0	.039 1.0		1000
	RVBL3-5	RVL3-5	#10	.209 5.3	.472 12.0	.370 9.4	1.118 28.4						1000
	RVB3-6	RV3-6	1/4	.252 6.4									1000
	RVB3-8	RV3-8	5/16	.331 8.4	.591 15.0	.524 13.3	1.339 34.0						1000
	RVB3-10	RV3-10	3/8	.513 10.5									1000
	RVB3-12	RV3-12	1/2	.512 13.0	.756 19.2	.630 16.0	1.520 38.6						1000

(UL) (cUL) ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KS Terminals:](#)

[RV3-4](#) [RV3-6](#) [RV3-8](#) [RVL3-5](#) [RVS3-5](#)