



Insulated Crimping and Cutting Tool



The Klein Tools Insulated Crimping/Cutting Tool crimps wire from 10 to 22 AWG. This crimper/cutter features a tapered nose for working in confined spaces. Additionally, it features bright orange outer coating on the handles that is flame retardant and impact resistant.

Specifications

Application:	10-22 AWG Insulated and Non-Insulated Solderless Terminals and Connectors	Special Features:	Flame Retardant and Impact Resistant Handle
Material:	Induction Hardened Steel	Insulated:	Yes
Joint Type:	Hot-Riveted	Nose Type:	Tapered
Cutting Capacity:	10-22 AWG Insulated and Non-Insulated Terminals	Crimping Capacity:	10-22 AWG Insulated and Non-Insulated Terminals
Standard:	IEC 60900 and ASTM F1505	Handle Color:	Orange
Handle Finish:	2-Layer Insulation	Handle Material:	High-Dielectric Plastic Cushion Grip
Overall Length:	10" (25.4 cm)	Weight:	1.0 lb (0.5 kg)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[1005-INS](#)