










VIEW F



SECTION A-A



OVERALL DIMENSION FOR MOUNTABILITY



ASSOCIATED PARTS (FOR INFORMATION)					
SECTION		SICMA 1.5 FEMALE TERMINAL	INSULATION DIAMETER OF WIRE		
		APTIV P/N			
0.35 - 0.70 mm ²		13761154	1.25-2.1		
1.35 - 2.0 mm ²		13761648	2.1-2.8		
TITLE			ASSOCIATED DOCUMENTS		
CABLE SEAL Ø 1.25-1.9			10736278		
CABLE SEAL Ø 1.75-3.0			10736279		

FEMALE CONNECTOR 8 WAY	03	CONNECTOR SEAL	13800056	SILICONE	BLUE
	02	PLR	13800060	PBT	YELLOW
	01	FEMALE HOUSING	13800066	PBT	GREY
			13800049	PBT	BLACK
	POS.	DESCRIPTION	APTIV PART NUMBER	MATERIAL	COLOR

NOTE	SPECIFICATIONS
1	FEMALE CONNECTOR ACCORDING TO: - TEMPERATURE CLASS T3 - ENGINE VIBRATOR CLASS V2 - SEALING CLASS 2
2	USER'S MANUAL: 13800047-CUS76
3	FEMALE CONNECTOR AND CAVITY'S POSITION ACCORDING TO: 13800035-CUS02
4	WIRE DIAMETER 0.35-0.70mm ² MINI= Ø 1.25 MAXI= Ø 2.1 1.35-2.0mm ² MINI= Ø 2.1 MAXI= Ø 2.8
5	DELIVERY CONNECTOR WEIGHT : 8.54g
6	NO WAFER HINGE OR WAFER HINGE BROKEN ALLOWED
7	VISUAL DEFECTS ON NO FUNCTIONAL AREAS ALLOWED
8	MATERIAL CODE
9	TOOL CAVITY NUMBER
10	PART CAVITY NUMBER
11	INDEX REPLACEMENT INSERT
12	DATE STAMP MONTH/YEAR
13	SPC: STATISTICAL PROCESS CONTROL

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.
CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.




CHART E					
> 70 100	>100 150	>150 200	>200 250	>250 300	>300 400
UNLESS OTHERWISE SPECIFIED					
±0.4	±0.5	±0.6	±0.8	±1	±1.2
ANGULAR TOLERANCE ±2°					

3				2				1							
DWG STATUS				REVISION HISTORY				AUTH		DR		APVD			
DATE	STG	REV	N/P/CHG	ZONE											
070C20	R	01		INITIAL RELEASE						P.BAL		M.SKR			
												APVD 1		APVD 2	
3D VIEW												SCALE 1:1			
												DISTR CODE			
												ROUTING			
												UNLESS OTHERWISE SPECIFIED			
												GENERAL TOLERANCES ACCORDING TO:		SEE CHART	
GD&T ACCORDING TO: ISO 1101															
REFERENCE															
FIRST ANGLE PROJECTION															
DO NOT SCALE															
USE MATH DATA															
												DATE			
												070C20			
												070C20			
												070C20			
MATERIAL															
SEE TABLE															
DRAWING NAME															
FEMALE CONNECTOR 8 WAY SEALED															
SICMA 3 1.5															
DRAWING NUMBER															
13800047															
SIZE															
A1															
SCALE															
2:1															
FRAME NO															
1 OF 1															
SHEET NO															
1 OF 1															
STG															
R 01															

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13800072](#)