







TYPE 102  
SAME AS TYPE  
EXCEPT AS SH  
WITHOUT CP




TYPE 106  
SAME AS TYPE 10  
EXCEPT AS SHOWN  
WITHOUT CPA





TYPE 110  
SAME AS TYPE 10  
EXCEPT AS SHOWN





TYPE 114  
SAME AS TYPE 1  
EXCEPT AS SHOWN




TYPE 118  
SAME AS TYPE 10  
EXCEPT AS SHOWN  
WITHOUT CPA




ASSEMBLY VIEW  
FOR REFERENCE ONLY



TYPE 103  
SAME AS TYPE  
EXCEPT AS SH  
WITHOUT CP




TYPE 107  
SAME AS TYPE 1  
EXCEPT AS SHOWN





```

      TYPE 111
      SAME AS TYPE 101
      EXCEPT AS SHOWN


```




TYPE 115  
SAME AS TYPE 1  
EXCEPT AS SHOWN




TYPE 101




- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
- DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (USE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN, USE REQUIRED FOR TOOL BUILD. USE MATH MODEL FOR PRECISE TOOL PATH DATA.
- WHEN PARTS ARE SHIPPED THEY MUST BE PACKED IN PLASTIC BAGS OR SHIPPING CONTAINERS MUST BE LINED WITH PLASTIC LINERS. BAGS OR LINERS MUST BE SEALED TO AVOID FOREIGN MATTER.
- THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
- FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
- THE FORCE TO DISENGAGE THE SECONDARY LOCK CAN BE BETWEEN 8 AND 13N.
- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMSHES, OR SURFACE FIBERS, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER ENP-4-3.CS.01.EN.
- SEALING CODE 3 : DESIGN WILL PASS SALT FOG AND IMPERSON TEST AFTER CONDITIONING AS SPECIFIED IN ENP-4-3.CS.01.EN (MATERIAL PACK), ENP-4-650 UNDERHOO MICRO-PACK, C-4006 WORLD CONNECTOR, ETC. WHEN MATED TO MATING PART OR EQUIVALENT




TYPE 104  
SAME AS TYPE  
EXCEPT AS SHC  
WITHOUT CPA




TYPE 108  
SAME AS TYPE 107  
EXCEPT AS SHOWN




TYPE 112  
SAME AS TYPE 101  
EXCEPT AS SHOWN



TYPE 116  
SAME AS TYPE 10  
EXCEPT AS SHOWN



SECTION A - A



|          |    |     |     |           |           |                |            |               |          |                  |  |
|----------|----|-----|-----|-----------|-----------|----------------|------------|---------------|----------|------------------|--|
| 3581B45  | 01 | -   | 101 | 116       | 36769.37  | 36769.35       | 36769.34   | 36769.33      | 33357593 |                  |  |
| 35512635 | 01 | -   | 118 | 136769.37 | 36769.35  | 36769.34       | 35512834   |               |          | 1,-2,-9,11       |  |
| 35061320 | 00 | AA  | 117 | 33177920  | 36769.35  | 36769.34       | 35061297   |               |          | 3,4,6,7,10,12    |  |
| 35061320 | 00 | AA  | 117 | 33177920  | 36769.35  | 36769.34       | 35061297   |               |          | 4,4,6,10,12      |  |
| 35062626 | 02 | -   | 115 | 36769.37  | 36769.35  | 36769.34       | 35022728   |               |          | 10,6,9,12        |  |
| 35066667 | 01 | -   | 114 | 36769.37  | 36769.35  | 36769.34       | 35022727   |               |          | 10,6,9,12        |  |
| 35067800 | 01 | AB  | 118 | 33177920  | 36769.35  | 36769.34       | 35067800   |               |          | 1,2,4,6,10,12    |  |
| 33178000 | 01 | AB  | 101 | 33177919  | 36769.35  | 36769.34       | 33178000   |               |          | 1,2,4,6,10,12    |  |
| 33212451 | 01 | AA  | 113 | 36769.37  | 36769.35  | 36769.34       | 33212451   |               |          | 5,1,12           |  |
| 33212451 | 01 | AA  | 113 | 36769.37  | 36769.35  | 36769.34       | 33212451   |               |          | 5,1,10,11,12     |  |
| 33107730 | 01 | AB  | 111 | 36769.37  | 36769.35  | 36769.34       | 33107730   |               |          | 5,6,8,10,11,12   |  |
| 33107730 | 01 | AB  | 111 | 36769.37  | 36769.35  | 36769.34       | 33107729   |               |          | 5,6,8,10,11,12   |  |
| 33102684 | 01 | AC  | 110 | 36769.37  | 36769.35  | 36769.34       | 33102683   |               |          | 5,6,8,10,11,12   |  |
| 33102684 | 01 | AC  | 110 | 36769.37  | 36769.35  | 36769.34       | 33102683   |               |          | 5,6,8,10,11,12   |  |
| 15549978 | 02 | AC  | 107 | 36769.37  | 36769.35  | 36769.34       | 15549977   |               |          | 1,2,4,6,10,12    |  |
| 33109148 | 01 | AB  | 108 | 36769.37  | 36769.35  | 36769.34       | 33109147   |               |          | 1,8,9,12         |  |
| 33109148 | 01 | AB  | 108 | 36769.37  | 36769.35  | 36769.34       | 33109147   |               |          | 1,8,9,12         |  |
| 13881217 | 01 | AA  | 098 | 36769.37  | 36769.35  | 36769.34       | 13880888   |               |          | 2,3,4,5,6,12     |  |
| 13833031 | 01 | AC  | 103 | 36769.37  | 36769.35  | 36769.34       | 13833308   |               |          | 1,8,9,12         |  |
| 13833031 | 01 | AC  | 103 | 36769.37  | 36769.35  | 36769.34       | 13833308   |               |          | 1,8,9,12         |  |
| 13820423 | 02 | AB  | 103 | 36769.37  | 36769.35  | 36769.34       | 13820420   |               |          | 1,2,5,6,8,12     |  |
| 13820423 | 02 | AB  | 103 | 36769.37  | 36769.35  | 36769.34       | 13820420   |               |          | 1,2,5,6,8,12     |  |
| 36769.35 | 01 | AF  | 02  | 36769.37  | 36769.35  | 36769.34       | 36769.33   |               |          |                  |  |
| 36769.35 | 01 | AF  | 02  | 36769.37  | 36769.35  | 36769.34       | 36769.33   |               |          |                  |  |
| PAR      | NO | REV | MP  | TYPE      | CONNECTOR | CONNECTOR SEAL | CABLE SEAL | STRAIN RELIEF | CPA      | BLOCKED CAVITIES |  |

[illegible][illegible]



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13820424](#)