






FCI
MASTER COPY
WHEN IN RED

UNCONTROLLED

NOTES:

ASSEMBLY FORCES

INSERTION ON # 10 PIN = 62.3N MAX

REMOVAL = 26.7-62.3N

SCD-1017-12	10
INTERLOCK PART NO	GRIP CODE

6674	5/19/04	REL-1	-	REDRAWN IN PRO-E AND DIMENSIONED IN METRIC ONLY. 0.3376 TO WAS 0.33		T.ANGER	S.SIAN	S.SIAN
ECN NUMBER	DATE	W-D-T	REVISION	ZONE	CHANGE DESCRIPTION	DRAWN BY	CHK BY	APPR BY
PRODUCT SPEC.		PACKAGING SPEC.		APPLICATION SPEC.		THIS DRAWING AND ALL OTHER INFORMATION CONTAINED HEREIN IS PROPRIETARY AND THE PROPERTY OF FCI. FCI's drawing may not be copied, reproduced or distributed to any third party without FCI's express written permission of FCI.		
10 PIN RECEPTACLE		N/A		N/A		© FCI April 1998		
TOLERANCES: $\pm 0.004 \pm 0.005$ HOLE $\pm 0.004 \pm 0.005$ ANGLE ± 0.004		MATERIAL: CDA 422 H040		SURFACE FINISH: 0.004 $\pm$ 0.015				CON SYSTEM:
CONTINUED NO.		COLOR: -		ECO Lvs. Ctds: N/A				 3RD ANGLE  DIMENSION IN MILLIMETERS
DO NOT SCALE DRAWING		TOOL NO. 0 088		ECO Lvs. Ctds: N/A		DRAWING NUMBER		SHEET
DATE		TITLE				DRAWING NUMBER		
5/14/84		M. WEBER		# 10 PIN RECEPTACLE (CONNECTOR TERMINAL)		SCD-1017-12		1
CHECKED						CONNECTOR TERM		SCALE: A
APPROVED		ESR NO. 6243		CAT. NO. -		FILE NAME		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[SCD-1017-12](#)