



MATING END



CABLE END



1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:




DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. MATERIAL RECYCLING CODE PER ISO 11469. (1.0901X1.004) CHARACTERS
AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
3. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR
IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR
BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE
FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP 4.7-CS-01.
4. (1.0901X1.004) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY
EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED"
OR NO LOGO.
5. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.

08917165	P	-	OBSELETE	POLYPROPYLENE COMPOUND BEIGE	2.541
06294879	P	-	OBSELETE	POLYPROPYLENE COMPOUND ORANGE	2.541
06288184	P	-	OBSELETE	POLYAMIDE COMPOUND NATURAL	2.541
02965151	P	-	OBSELETE	POLYPROPYLENE COMPOUND NATURAL	2.541
02962515	P	-	OBSELETE	POLYPROPYLENE COMPOUND GRAY	2.541
02962514	P	-	OBSELETE	POLYPROPYLENE COMPOUND AMBER	2.541
02962513	P	-	OBSELETE	POLYPROPYLENE COMPOUND GREEN	2.541
02962512	P	-	OBSELETE	POLYPROPYLENE COMPOUND BLUE	2.541
02962511	P	-	OBSELETE	POLYPROPYLENE COMPOUND RED	2.541
02962510	P1	-	-	POLYPROPYLENE COMPOUND BLACK	2.541
02962449	P4	-	-	POLYPROPYLENE COMPOUND NATURAL	2.541

PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	VOLUME CM ³
---------	-----	-----	--------	----------------------------------	------------------------

SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	11
	LAST NO. USED	11

MISSING SYMBOLS		DWG STATUS				ZONE	REVISION HISTORY				AUTH	DR	IP/D/A/D	
		DATE	STG	REV	N/P	CHG								
NO MISSING SYMBOL NUMBER		25MR09	R	01	-	-	ALL ACTIVE PARTS - CLEARED REV COLUMN, REDRAWN TO PD & UPDATED PDM ATTRIBUTES				407629	HRS	SLG	A
		05MY09	R	02	-	-	02962449 - UPDATED PDM ATTRIBUTES				407912	EGR	JVM	W

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CPI)		DISTR CODE	
SEE CHART		D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-1994 AS MODIFIED BY THE AN GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM (CPI). SEPARATE PATTERNING OF DIMENSIONS SHALL BE GIVEN SEPARATELY REGARDLESS OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN INCHES			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE USE MATH DATA	
		 	

DELPHI									
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH									
					DATE				
DR									
APV01		LIST			15AP65				
APV02		KENNEDY			19AP65				
APV03		KENNEDY			19AP65				
APV04									
APV05									
SUBSTANCES OF ORIGIN AND RECYCLED CONTENT PER DELPHI 10949001									
MATERIAL SEE CHART									
DRAWING NAME									
TAXI CONN F 56 SERIES									
DRAWING NUMBER									
02962823									
SIZE A0		SCALE 5:1		FRAME 1 OF 1		SHEET 1 OF 1		STG R02	
								REV N/P	
								-	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[02962510](#)