


3

2

1

| PART NO. | TREAT. & FIN. | APPLICABLE WIRE SIZE | W ₁ | H ₁ | W ₂ | H ₂ |
|--------------|---------------|----------------------|----------------|----------------|----------------|----------------|
| 7114-2882 | | | | | | |
| 7114-2882-02 | TIN PLATED | CAVUS 0.3~AV 0.5 | 2.7 | 2.5 | 3.8 | 3.5 |
| 7114-2883 | | | | | | |
| 7114-2883-02 | TIN PLATED | CAVUS 0.85~AV 2 | 3.7 | 3.4 | 5.5 | 4.8 |



| DATE | REVISION RECORD | NO. | CHKD | CUSTOMER | CUSTOMER PART NO. | CUSTOMER DWG NO. | MATL. SPEC. | TREAT. & FIN. | ISSUE MARK | |
|-------------------------|----------------------------------|-----------------|--------|----------|------------------------|------------------|------------------------------|---------------|------------|------------|
| 2012/02/21 | CHANGED MATERIAL INDICATION ETC. | C.12-Z269 | E. I | | | | BRASS | | | |
| 1993/03/19 | ADDED PART NO. | C93-6368 | M. K | | | | (t=0.4) | | SEE TABLE | |
| 1990/09/06 | NEW | C90-7210 | M. K | | | | | | | |
| LET | DATE | REVISION RECORD | NO. | CHKD | OFFICE | TRIAL PART NO. | NAME M-US TYPE TERMINAL MALE | | | |
| GENERAL TOLERANCE | | | | VENDOR | | | | | | |
| 10MAX | 50MAX | 100MAX | 250MAX | 2500VR | DWG TYPE | DWG SOURCE | DWG DATE | UNIT | SCL | ANGLE |
| ±0.15 | ±0.2 | ±0.3 | ±0.5 | ±0.75 | R | NEW | 1990/09/06 | mm | 2:1 | 3 |
| A | ±0.2 | ±0.3 | ±0.55 | ±0.95 | APPROVED | CHECKED | CHECKED | DESIGN | DRAWN | |
| B | ±0.3 | ±0.5 | ±0.8 | ±1.4 | M. KASHIYAMA Y. FUKASE | | K. JINNO | | E. ITALIA | |
| ◎ | ±0.3 | ±0.5 | ±0.8 | ±1.4 | 2012/02/21 | | 2012/02/21 | | 1989/04/04 | 2012/02/21 |
| SPECIFIED MASS | | | | | | | | | | |
| PART NO. 7114-2882 ETC. | | | | | | | | | | |
| CH. CODE 7114-2882 : R | | | | | | | | | | |
| DWG NO. 7114-2882 : R | | | | | | | | | | |
| SET DWG NO. | | | | | | | | | | |
| YAZAKI CORPORATION | | | | | | | | | | |

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Yazaki:](#)

[7114288302](#) [7114288202](#)