

PART NO. AND CH. CODE	W ₁	W ₂	H ₁	H ₂	R ₁	R ₂	L	△(REFERENCE) WIRE SIZE (mm ²)
7114-4100-08. ㊦	2.50	2.80	(2.40)	(3.50)	0.45	0.45	9.10	△0.3~0.5 EQUIVALENT
7114-4101-08. ㊦	3.30	3.40	(3.25)	(4.10)	0.65	0.65	9.90	△0.6~1.25 EQUIVALENT

△GENERAL TOLERANCE									
	10MAX	50MAX	100MAX	250MAX	250OVR	R5MAX	R10MAX	R20MAX	R200VR
A	±0.15	±0.2	±0.3	±0.5	±0.75				
B	±0.2	±0.3	±0.55	±0.95	±1.4	±0.2	±0.3	±0.5	±2.5
(C)	±0.3	±0.5	±0.8	±1.4	±2				

注記



1. 嵌合端子番 : 7116-4100-08 ETC.

△△2. 材質 : 銅合金 t=0.3 (金めっき、スズめっき)


NOTES

1. MATING TERMINAL NO. : 7116-4100-08 ETC.


△△2. MATERIAL : COPPER ALLOY t=0.3
(GOLD PLATING, TIN PLATING)




APPLICABLE WIRE SIZE MARK




(7114-4100-08)



(7114-4101-08)



SEC. A-A



SEC. B-B

△	05/10/18	DELETED SOLDER PLATING INSTRUCTION, ETC.	C05-ZD50	Y. W
△	04/06/25	CHANGED WIRE SIZE	C04-Z636	H. T
△	03/12/23	CORRECT MISENTRY	C04-P010	M. H
△	03/09/19	CHANGED NOTE. ㊦	C03-X584	H. T
△	03/07/22	CHANGED WIRE SIZE & FORM	C03-X482	K. O
△	96/01/16	CHANGED FORM	C96-L043	A. Y
△	95/09/06	NEW	C95-M060	Y. W
LET	DATE	REVISION RECORD	NO.	CHKD

GENERAL TOLERANCE						
	10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'
(C)	±0.3	±0.5	±0.8	±1.4	±2	±30'

SPECIFIED

MASS

CUSTOMER		CUSTOMER PART NO.		CUSTOMER DWG NO.	
OFFICE		TRIAL PART NO.		VENDOR NO.	
DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
R	NEW	95/09/06	mm	5:1	3
APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	
	和田	酒井	K. OHTAKA	O. DAR	
05.11.1	05.10.28	05.10.28	95/05/29	05/10/18	

MATL. SPEC.	SEE NOTES	TREAT. & FIN.
NAME 1.5 SYSTEM CONNECTOR		
TERMINAL (M) (GOLD PLATING)		
PART NO. CH. CODE	7114-4100-08 ETC.	
DWG NO.	7114-4100-08:R	SET DWG NO.
YAZAKI CORPORATION		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Yazaki:](#)

[7114410108](#) [7114410008](#)