



| YAZAKI PART NO. | COLOR |
|-----------------|---------|
| 7122-1460 | NATURAL |
| 7122-1460-30 | BLACK |
| 7122-1460-40 | GRAY |
| 7122-1460-50 | ORANGE |
| 7122-1460-60 | GREEN |
| 7122-1460-70 | YELLOW |
| 7122-1460-80 | BROWN |
| 7122-1460-90 | BLUE |

NOTES

- 1)MATING PART NO. :7123-1460 ETC.
- 2)APPLICABLE TERMINAL NO. :7114-1170
:7114-1171

注記

- 1)嵌合相手品番:7123-1460 ETC.
- 2)適用端子品番:7114-1170, 7114-1171

| LET | DATE | REVISION RECORD | NO. | CHKD |
|-----|----------|-----------------|----------|------|
| | 88.09.22 | NEW | BMC-3105 | T.M |

| GENERAL TOLERANCE | | | | | | | | | |
|-------------------|-------|-------|--------|--------|--------|-------|--------|--|--|
| | 10MAX | 50MAX | 100MAX | 250MAX | 2500VR | ANGLE | ECCENT | | |
| A | ±0.15 | ±0.2 | ±0.3 | ±0.5 | ±0.75 | ±30° | 0.1 | | |
| B | ±0.2 | ±0.3 | ±0.55 | ±0.95 | ±1.4 | ±30° | 0.1 | | |
| ◎ | ±0.3 | ±0.5 | ±0.8 | ±1.4 | ±2 | ±30° | 0.15 | | |
| SPECIFIED | | | | | WEIGHT | | | | |

| | | | | | |
|-------------------|--|-------------|--|---------------------|--|
| CUSTOMER | | MATERIAL | | TREAT. | |
| CUSTOMER PART NO. | | SPEC. | | NYLON | |
| OFFICE | | NAME | | & FIN. | |
| VENDOR | | STD LIB NO. | | 6P 090 MALE HOUSING | |
| VENDOR NO. | | PART NO. | | 7122-1460 ETC. | |
| DWG TYPE | | DWG SOURCE | | DWG NO. | |
| R | | NEW | | 7122-1460-R | |
| APPROVED | | CHECKED | | DESIGN | |
| 加藤 前島 | | KANeko | | DRAWN | |
| 88.09.27 | | 88.09.23 | | S. YAGI | |
| 88.09.27 | | 88.09.23 | | YAZAKI CORPORATION | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Yazaki:](#)

[71221460](#)