



SEC. A-A

TABLE 1

SUB ASSEMBLY PART NO. AND CH. CODE	NO.	PART NO. AND CH. CODE	PART NAME	MATERIAL	COLOR	QTY.
SEE TABLE 2	①	SEE TABLE 2	HOUSING	PBT	SEE TABLE 2	1
	②	7158-5957	FRONT HOLDER	PBT	NATURAL	1
	③	7158-5958	SPACER	PBT	NATURAL	1

TABLE 2

SUB ASSEMBLY PART NO. AND CH. CODE	PART NO. AND CH. CODE	COLOR
7283-8117, [B]	7183-8117	NATURAL
7283-8117-30, [B]	7183-8117-30	BLACK

注記

- ③ 1. かん合相手品番 : 7382-8117、7382-8315
2. 適用端子品番 : 7116-4660-02 ETC.

NOTES

- ③ 1. MATING PART NO. : 7382-8117, 7382-8315
2. APPLICABLE TERMINAL NO. : 7116-4660-02 ETC.

GENERAL TOLERANCE

	10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±0.2	±0.3	±0.5	±2.5	±3°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±0.2	±0.3	±0.5	±2.5	±3°	0.1
C	±0.3	±0.5	±0.8	±1.4	±2	±0.2	±0.3	±0.5	±2.5	±3°	0.15

③	07/07/23	ADDED COLOR PART NO., ETC.		C07-Z634	M. M	CUSTOMER				MATL. SPEC.				SEE TABLE	TREAT. & FIN.		
②	04/01/09	CHANGED FORM ETC., [B]		C03-X804	T. I	CUSTOMER PART NO.				CUSTOMER DWG NO.							
①	02/08/26	CHANGED FORM, [A]		C02-X822	S. K									NAME			
	02/04/11	NEW		C02-X358	S. K	OFFICE				TRIAL PART NO.				025 6P CONNECTOR FEMALE			
LET	DATE	REVISION RECORD		NO.	CHKD	VENDOR								SUB ASSEMBLY			
GENERAL TOLERANCE						VENDOR NO.											
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE		DWG DATE	UNIT	SCL	ANGLE	PART NO.		
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	NEW		02/04/11	mm	2/1	3	CH. CODE	③ 7283-8117 ETC.	
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN		DWG NO.	7283-8117:R		
C	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15	杉山(電)		—		杉山		S. KAYAMA	C. REPOLLO	SET DRW NO.	
SPECIFIED						MASS		07.07.27		07.07.25		01/10/31		07/07/23		YAZAKI CORPORATION	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Yazaki:](#)

[72838117](#)