



QBIP-6210A

3.5" SubCompact Board with Intel® Celeron® N6210 Processor, Dual Channel DDR4 memory, 4 x COM , 1 x SATA 6Gb/s, 4 x USB 3.2 Gen 1, 2 x USB 2.0



Specifications

Form Factor	3.5" SBC 146W x 101.7Dmm
CPU	Intel® Celeron® N6210 Processor 10nm, 2 cores, 2 threads, up to 2.60 GHz TDP 6.5W
Socket	1 x FCBGA1493
Chipset	—
Memory	2 x DDR4 SO-DIMM sockets, Max. Capacity 32 GB Support Dual Channel DDR4 3200MHz memory modules
Ethernet	2 x GbE LAN Ports (Intel® I211AT)
Video	Integrated Graphics Processor - Intel® UHD Graphics for 10th Gen Intel® Processors: 2 x HDMI 2.0 port, supporting a maximum resolution of 4096x2160 @60Hz 1 x LVDS port, supporting a maximum resolution of 1920x1080 @60Hz (3 independent display outputs)

Features


- 3.5" SBC
- Intel® Celeron® N6210 Processor
- Dual Channel DDR4, 2 x SO-DIMMs
- 2 x GbE LAN Ports
- 1 x SATA 6Gb/s Port
- 2 x HDMI, LVDS ports for multiple display
- 1 x COM Port (RS-232/422/485 & RI/5V/12V)
- 1 x COM Port (RS-232/422/485)
- 2 x COM Ports (RS-232)
- 4 x USB 3.2 Gen 1

Audio	Realtek® Audio codec
Storage	1 x SATA 6Gb/s Port
Raid	—
Expansion Slots	1 x 2280 M.2 M-Key (SATA 6Gb/s, support NVMe SSD) 1 x Full-size mini PCIe with SIM slot
Internal I/O	1 x 4-pin box power connector (+9V~36VDC) 1 x SATA Power header 1 x CPU fan header 1 x Front panel header 1 x Front panel audio header 1 x 2W Speaker out header 2 x USB 2.0 headers 1 x COM header (RS-232/422/485 & RI/5V/12V) 1 x COM header (RS-232/422/485) 2 x COM headers (RS-232) 1 x Backlight Control header 1 x AT/ATX mode select jumper 1 x GPIO (8 bits) & SMBus header 1 x Buzzer header
Rear I/O	1 x Headphone Jack 2 x HDMI 2 x RJ45 LAN Ports 4 x USB 3.2 Gen 1
TPM	—
OS Compatibility	Windows® 10 (x64)
Operating Properties	Operating temperature: 0°C to 60°C Operating humidity: 0-90% (non-condensing) Non-operating temperature: -40°C to 85°C Non-operating humidity: 0%-95% (non-condensing)

GIGAIPC reserves the right to modify or change technical data without prior notice.

Dimension

Unit: mm



Packing Content

- Carton size: 465 x 351 x 217 (mm)
- Packing Capacity: 10pcs
- Including:
 - SATA Power cable x 1 (P/N: 25CRI-200B02-K1R)

Order Information

- Motherboard: 9MEHLNASMR-SI (Box packing)

Optional Kit

- Fanless Heatsink P/N: 25ST1-12311B-A7R
- Fansink P/N: 25ST4-1231Z0-A7R

2022/06/14

GIGAIPC reserves the right to modify or change technical data without prior notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

GIGAIPC:

9MEHLNASMR-SI