



TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.15
.XX	±0.10

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER	
ORIGINAL	①



SPECIFICATION:

MATERIAL:

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

HOUSING: PA9T, BLACK

MAGNET: N52 PULL3-3.5N

ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 5V

RATED CURRENT (PER CONTACT): 2A

INSULATION RESISTANCE: 100MEGAOHMS MINIMUM.

DIELECTRIC WITHSTANDING VOLTAGE: 100V AT 60Hz.

CONTACT RESISTANCE: 30mOHMS MAX. BEFORE TEST AND 60mOHMS MAX.

AFTER TEST POGO PIN WORKING STROKE.



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

MAGNETIC SPRING LOADED CONNECTOR, 3POS, MALE

ACAD REFERENCE NO.: 685F0321451110E		UNIT: MM
DRAWN: J.L.	DATE: 4/14/2023	
CHECKED: R.S.M	DATE: 4/14/2023	
SCALE: (IN CAD 1:1)	SHEET 1 OF 1	
DRAWING NUMBER: 685F0321451110E		ISSUE 1
PART NUMBER: 685F0321451110E		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EDAC:

685F0321451110E