









PANEL MOUNTING

DPDT  
CONTACT CONFIGURATION

## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 5A @ 250 VAC  
6A @ 24 VDC  
8A @ 125 VAC
5. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES  
AT FULL LOAD.
6. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
7. OPERATING TEMP.: -20°C to 55°C
8. SEAL RATING: IP 40
9. (MOUNTING) PANEL THICKNESS: 0.5 - 5.0 mm
- ▲10. LAMP VOLTAGE: 28V DC (40mA) INCANDESCENT
11. ▲ DENOTES CRITICAL PARAMETER.
12. 2002/05/EC (ROHS) COMPLIANT.
13. PACKAGE: BOX/20 PIECES PER BOX



## PARTS LIST

| ITEM | QTY | PART NUMBER | DESCRIPTION                                |
|------|-----|-------------|--------------------------------------------|
| 1    | 1   | F040023     | D16EET12                                   |
| 2    | 1   | F050405     | 5000405 - 28VDC INCANDESCENT - 40mA        |
| 3    | 1   | F052206     | 5000206 - RECT. OPAQUE YEL. LENS (CONCAVE) |



TITLE D16EET12CYEL

|     |        |                         |         |     |
|-----|--------|-------------------------|---------|-----|
| A   | 18387  | RELEASED FOR PRODUCTION | 2/11/09 | BLR |
| REV | PCR NO | DESCRIPTION             | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|       |           |     |         |     |
|-------|-----------|-----|---------|-----|
| SCALE | DATE      | DR  | DWG     | REV |
| 1.5:1 | 2/11/2009 | BLR | XF0781P | A   |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[D16EET12CYEL](#)