



1 0 1 0 2
3 0 0 4
a-L-b (+)

SPST
CONTACT CONFIGURATION

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. RATINGS: 5A @250V AC
8A @125V AC
4. CONTACT MATERIAL:
COPPER ALLOY W/Silver Plating
5. LAMP VOLTAGE: 24V DC

PARTS LIST			
ITEM	QTY.	PART NO.	PART DESCRIPTION
1	1	F040009	D16 OA R1 1
2	1	F050423	50-004-23 (RED LED)
3	1	F050104	50-001-04 (Transparent RED lens)



RECOMMENDED PANEL MOUNTING
SCALE 1:1

E-SWITCH®

TITLE			
D16 OA R11 K RED RED TRANSPARENT /CONCAVE LENS			
REV.	ECN No.	DATE	CHKD
A	12596	11/26/02	CJB
RELEASED FOR PRODUCTION			
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE	DATE	DR	DWG
1.5:1	11/26/02	CB	XF0529P
			REV
			A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[D16OAR11KREDRED](#)