




PARTS LIST



ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040027	D16OAR12
2	1	F050417	50-004-17 6VDC LED
3	1	F050104	50-001-04 ROUND RED LENS



PANEL MOUNTING



CONTACT CONFIGURATION



- NOTE:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 3. TERMINAL NUMBERS FOR REF ONLY
 4. MECHANICAL LIFE: 2,000,000 OPERATIONS
 5. INSULATION RESISTANCE: 1,000 MILLI-OHM MIN.
 6. OPERATING TEMP.: -25°C to 70°C
 - ▲ 7. LAMP VOLTAGE: 6VDC RED LED
 8. ▲ DENOTES CRITICAL PARAMETER.
 9. PACKAGE: BOX/20 PCS. PER
 10. 2002/95/EC (ROHS) COMPLIANT.



A	17458	RELEASED FOR PRODUCTION	7/12/07	TN
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE D16OAR12HREDRED

SCALE 2:1	DATE 7/12/2007	DR TN	DWG XF0729P	REV A
--------------	-------------------	----------	----------------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[D16OAR12HREDRED](#)