









PANEL MOUNTING



DPDT  
CONTACT CONFIGURATION



| PARTS LIST |     |             |                            |
|------------|-----|-------------|----------------------------|
| ITEM       | QTY | PART NUMBER | DESCRIPTION                |
| 1          | 1   | F040027     | D16OAR12                   |
| 2          | 1   | F050422     | 50-004-22 24VDC GREEN LED  |
| 3          | 1   | F050102     | 50-001-02 ROUND GREEN LENS |

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. MECHANICAL LIFE: 2,000,000 OPERATIONS
5. INSULATION RESISTANCE: 1,000 MILLI-OHM MIN.
6. OPERATING TEMP.: -25°C to 70°C
- ▲ 7. LAMP VOLTAGE: 24VDC GREEN LED
8. ▲ DENOTES CRITICAL PARAMETER.

**E-SWITCH®**

|     |        |                         |           |    |
|-----|--------|-------------------------|-----------|----|
| A   | 14521  | RELEASED FOR PRODUCTION | 11/18/004 | AR |
| REV | PCR NO | DESCRIPTION             | DATE      | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE D16OAR12KGRNGRN

SCALE 2:1

DATE 11/18/04

DR AR

DWG XF0614P

REV A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[D16OAR12KGRNGRN](#)