



- NOTE:**
1. ALL DIMENSIONS IN MM[INCH].
 2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
 3. TERM. NOS. FOR REFERENCE ONLY.
 - ▲ 4. CONTACT MATERIAL: GOLD FLASH
 5. CONTACT RATING: 150mA, 250VAC/DC
350mA, 110VAC/DC
 6. CONTACT RATING (NON-SWITCHING) 5A
 7. OPERATING FORCE 800± 300gf-cm
 8. OPERATING TEMP: -30°C to 85°C
 - ▲ 9. CIRUIT 3P: 3 POSITION 30° INDEX
 10. DIELECTRIC STRENGTH: 1000V RMS MIN.@ SEA LEVEL
 - ▲ 11. HARDWARE SUPPLIED ON SWITCH:
STOP RING, LOCKWASHER, HEXNUT
 12. ▲ DENOTES CRITICAL PARAMETER.



A	22669	RELEASE FOR PRODUCTION	2/14/17	MW
REV	PCR NO	DESCRIPTION	DATE	BY

E-SWITCH®				
TITLE KC33B30.002NLF				
SCALE	DATE	DR	DWG	REV
3:2	2/13/2017	MW	G510614	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[KC33B30.002NLF](#)