


SCHEMATIC



SPECIFICATIONS

FUNCTION:  
1P1T OFF-ON

RATINGS:  
ANSI/UL 1054 AND CAN/CSA C22.2 NO. 55 (E194579):  
10A 125VAC [UR, cUR]

CONTACT RESISTANCE:  
INITIAL: 35mΩ Max. AT 50VAC

INSULATION RESISTANCE:  
100MΩ MIN. AT 500VDC

DIELECTRIC STRENGTH:  
1,500VAC FOR 1 Minute

ELECTRICAL LIFE:  
6,000 CYCLES [UR, cUR]

TEMPERATURE:  
OPERATING: -20°C TO 105°C [UR, cUR]

APPROVALS:





COLORS AND MARKINGS

BODY:  
**BLACK**


ACTUATOR:  
**BLACK**

MARKINGS:  
NO MARKINGS

MARKING COLOR:  
NONE



SUGGESTED PANEL CUTOUT



PANEL THICKNESS	X
0.030~0.049 [0.75~1.25]	0.756 [19.2]
0.049~0.079 [1.25~2.00]	0.764 [19.4]
0.079~0.118 [2.00~3.00]	0.772 [19.6]

ACTUATOR	A	09/30/16	MJR
BODY	A	09/30/16	MJR
COLORS	A	09/30/16	MJR
MATERIALS	A	09/30/16	MJR
SPECIFICATIONS	A	09/30/16	MJR
REFERENCE	REV.	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH-LAMB INDUSTRIES AND IS NOT TO BE COPIED OR TRANSFERRED

INITIAL RELEASE	100158	June 10, 2021	JM
DESCRIPTION	PCR	DATE	DRAWN BY

DIMENSIONS	INCHES [MILLIMETERS]
GENERAL TOLERANCES	±0.008 [±0.2] / ±1°
SCALE	DRAWING NOT TO SCALE

E-SWITCH®	LAMB INDUSTRIES
RD11131100	
ITEM NUMBER	38-RD11131100
DATE	June 10, 2021
REVISION	A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[RD11131100](#)