


SCHEMATIC



SPECIFICATIONS

FUNCTION:
1P1T OFF-ON

RATINGS:
ANSI/UL 1054 AND CAN/CSA C22.2 NO. 55 (E194579):
10A 125VAC [UR, cUR]

CONTACT RESISTANCE:
INITIAL: 35mΩ Max. AT 50VAC

INSULATION RESISTANCE:
100MΩ MIN. AT 500VDC

DIELECTRIC STRENGTH:
1,500VAC FOR 1 Minute

ELECTRICAL LIFE:
6,000 CYCLES [UR, cUR]

TEMPERATURE:
OPERATING: -20°C TO 105°C [UR, cUR]

APPROVALS:

 RoHS COMPLIANT



COLORS AND MARKINGS

BODY:
BLACK


ACTUATOR:
WHITE

MARKINGS:
NO MARKINGS

MARKING COLOR:
NONE



SUGGESTED PANEL CUTOUT




PANEL THICKNESS	X
0.030~0.049 [0.75~1.25]	0.756 [19.2]
0.049~0.079 [1.25~2.00]	0.764 [19.4]
0.079~0.118 [2.00~3.00]	0.772 [19.6]

ACTUATOR	A	09/30/16	MJR
BODY	A	09/30/16	MJR
COLORS	A	09/30/16	MJR
MATERIALS	A	09/30/16	MJR
SPECIFICATIONS	A	09/30/16	MJR
REFERENCE	REV.	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH-LAMB INDUSTRIES AND IS NOT TO BE COPIED OR TRANSFERRED

A	INITIAL RELEASE	22532	09/30/16	MJR
REV.	DESCRIPTION	PCR	DATE	DRAWN BY

DIMENSIONS	INCHES [MILLIMETERS]
GENERAL TOLERANCES	±0.008 [±0.2] / ±1°
SCALE	DRAWING NOT TO SCALE
PROJECTION	1st Angle

	
RD11131200	
ITEM NUMBER	38-RD11131200
DATE	SEPTEMBER 30, 2016
REVISION	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[RD11131200](#)