





P.C. MOUNTING

O.P. (MM)	P.T. (MM)
8.8 ±0.8	1.6 Max.




O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



CIRCUIT: SPDT
NORMALLY CLOSED

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X±0.4
X.XX±0.25
- RATING: 3A @125VAC
1.5A @250 VAC UL
- OPERATING FORCE: 40±10 GRAMS
- OPERATING TEMP: -25°C TO 75°C
- ELECTRICAL LIFE: 10,000 CYCLES MIN.
- INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
- DIELECTRIC STRENGTH: 500VAC - 1 MINUTE
- ▲ DENOTES CRITICAL PARAMETER.
- PACKAGED IN TRAYS, 120 PIECES PER TRAY



REV	ECO NO	DESCRIPTION	DATE	BY
B	ECO-102049	PRINT UPDATE	07/03/23	JS



E-SWITCH®

OBJECT ID
000021351

TITLE SS0750301F040V2A

SCALE 4:1

DATE 5/30/2012

DR DRG

DWG Q971035

REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[SS0750301F040V2A](#)