


P.C. MOUNTING






CIRCUIT: SPDT

O.P. (MM)	P.T. (MM)
9.65 ± 0.8	1.35 MAX.


O.P. = OPERATING POINT
P.T. = PRE-TRAVEL

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
- ▲ 3. RATING: 3A @125VAC
1.5A @250VAC UL
4. OPERATING FORCE: 50 ± 15 GRAMS
[.124 in]
5. OPERATING TEMP: -25°C TO +75°C
6. ELECTRICAL LIFE: 10,000 CYCLES MIN.
7. INSULATION RESISTANCE: 100 Mega-OHMS MIN AT 500VDC.
8. DIELECTRIC STRENGTH: 1500VAC - 1 MINUTE
9. CONTACT RESISTANCE: 100 Milli-OHMS MAX.
10. ▲ DENOTES CRITICAL PARAMETER.
11. PACKAGED IN TRAYS, 120 PIECES PER TRAY.
12. 2002/95/EC (ROHS) COMPLIANT



ISOMETRIC
SCALE: 3:1



A	20701	RELEASE FOR PRODUCTION	8/7/12	RC
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE SS0750303F050V2A

SCALE 4:1

DATE	8/7/2012
------	----------

DR	
RC	

DWG Q971036

REV
A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[SS0750303F050V2A](#)