



RECOMMENDED P.C.B. LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 50mA, @12V DC
5. TRAVEL: 0.30±0.15mm
6. OPERATING FORCE: 160±50gf
7. CONTACT RESISTANCE: 100 MILLIOHMS Max.
8. ELECTRICAL LIFE: 100,000 CYCLES MIN.



E-SWITCH®			
B	11825	REVISED DESCRIPTION	6/18/02 CJC
A	11825	RELEASED FOR PRODUCTION	11/08/01 CJC
REV.	ECN No.	DESCRIPTION	DATE CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE		DATE	DR
2:1		11/08/01	CJC
TITLE		DATE	DR
TL 1100 F160 Q (4J BLK)		11/08/01	CJC
DWG		DATE	DR
XP0025P		11/08/01	CJC
REV		DATE	DR
B		11/08/01	CJC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL1100F160Q4JBLK](#)