



- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
 3. RATING: 12VDC @ 50mA
 4. CONTACT RESISTANCE: 100mΩ MAX.
 5. INSULATION RESISTANCE: 100MΩ MIN.
 6. OPERATING FORCE: 160 ± 50gf
 7. TRAVEL: 0.2 ± 0.1mm
 8. OPERATING TEMPERATURE: -40°C to 85°C
 9. OPERATING LIFE 500,000 CYCLES
 - ▲ 10. LED COLOR: RED
 11. ▲ DENOTED CRITICAL PARAMETER
 12. 2011/65/EU (ROHS) COMPLIANT
 13. PACKAGE: 450 PIECES PER REEL.
 14. PART TO BE HALOGEN FREE.

ALL TERMINALS TO BE COPLANAR WITHIN 0.1mm(0.004")

LED SPECS	UNITS	RED
FORWARD CURRENT	mA	20
FORWARD VOLTAGE	V	1.95 TYP. - 2.5 MAX.
LUMINOUS INTENSITY	MCD	1800 TYP.



B	23036	update Package Note	10/9/17	MW
A	22935	New Release	7/21/17	rc
REV	PCR NO	DESCRIPTION	DATE	BY

TITLE TL3265RQNN				
SCALE	DATE	DR	DWG	REV
4:1	7/5/2017	rc	B200072	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL3265RQNN](#)