


 $17.60^{+.20}_{-.00}$
[.69^{+.008}_{-.000} in]


PANEL CUT-OUT
PANEL THICKNESS 1-10mm

 $\phi 19.00^{+.20}_{-.00}$
[$\phi .748^{+.008}_{-.000}$ in]

 $\phi 15.50$
[.61 in]

 $\phi 22.00$
[.87 in]

▲ POWER SYMBOL
ILLUMINATION
COLOR: RED

▲ ACTUATOR
BLACK ANODIZED






NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 3A 250 VAC cUL
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD
7. MECHANICAL LIFE: 1,000,000 CYCLES
8. INSULATION RESISTANCE: 1,000 M Ω @ 500VDC MIN.
9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
10. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
11. OPERATING TEMP.: -20°C to 55°C
12. ▲ DENOTES CRITICAL PARAMETER
- ▲ 13. LAMP VOLTAGE: 20mA 12V
14. TRAVEL: 3.2mm
15. ACTUATION FORCE: 2.5 $\pm$ 1.0 N
16. MOUNTING NUT TORQUE: 5-14 Nm
17. INGRESS PROTECTION: IP67
18. HARDWARE SUPPLIED: O-RING AND HEXNUT

2.0
[.08 in]

17.50 FLATS
[.69 in]

M19 x 1.0
THREAD



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
C	ECO-100350	UPDATE PANEL CUTOOUT	12/09/21	JS	TITLE ULV4F2B11514				000026096
					SCALE	DATE	DR	DWG	REV
					3:2	4/18/2017	MW	T940096	C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[ULV4F2B11514](#)