


O.P. (MM)	F.P. (MM)
6.40~6.95	7.35 MAX

O.P. = OPERATING POINT
F.P. = FREE-POSITION



▲ CIRCUIT: SPDT

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. RATING: 3A @ 12VDC OR 3A @ 125VAC, 250VAC
4. CONTACT RESISTANCE: 150mΩ MAX.
5. INSULATION RESISTANCE: 100MΩ @ 500VDC
6. DIELECTRIC STRENGTH: 500VAC FOR 1 MINUTE
7. ELECTRICAL LIFE: 100,000 CYCLES MIN.
8. MECHANICAL LIFE: 500,000 CYCLES MIN.
9. OPERATING TEMP: -40°C TO 85°C
10. MOISTURE PROTECTION: IP67
11. OPERATING FORCE: 130 gf MAX.
12. ▲ DENOTES CRITICAL PARAMETER.

REV	ECO NO	DESCRIPTION	DATE	BY				OBJECT ID	
A	ECO-100685	NEW RELEASE	03/14/22	MR				TITLE WS1085300F130SA	
<p style="font-size: small; text-align: center;">THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED</p>					SCALE	DATE	DR		
					2:1	1/24/2022	MJR	N010530	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[WS1085300F130SA](#)