






P.C. MOUNTING



ISOMETRIC



CIRCUIT: DPDT



- NOTES:
1. ALL DIMENSIONS IN MM[INCH]
 2. GENERAL TOLERANCE:
X.X = ± 0.4 X.XX = ± 0.25
 3. ▲ DENOTES CRITICAL PARAMETER
 4. TERM NOS. FOR REF ONLY
 5. RATING: .3A @ 6VDC
 - ▲ 6. OPERATING FORCE: 200 ± 150 GRAMS
 7. LIFE CYCLES: 10,000 CYCLES
 8. CONTACT RESISTANCE (INITIAL): 70m ohm MAX.
 9. 2002/95/EC (ROHS) COMPLIANT
 10. DIELECTIC STRENGTH: 500VAC FOR 1 MINUTE
 - ▲ 11. CONTACT PLATING: GOLD 4 MILLIONTHS MIN. OVER NICKEL



A	18241	RELEASE FOR PRODUCTION (WAS 2000916)	9/11/08	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

TITLE EG 2272				
SCALE	DATE	DR	DWG	REV
5:1	9/11/2008	BLR	P122713	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[EG2272](#)