




SIMATIC DP, ET200 PRO Fail-safe electronic module 8/16 F-DI 24 V DC
 PROFIsafe, 90 mm overall width, up to Category 4 (EN 954-1)/ SIL3
 (IEC61508)/PLE (ISO13849)

Supply voltage	
Rated value (DC)	24 V
Reverse polarity protection	Yes
power supply according to NEC Class 2 required	No
Input current	
from supply voltage 1L+, max.	120 mA; Typical
from backplane bus 3.3 V DC, max.	20 mA
Power loss	
Power loss, typ.	4.5 W
Digital inputs	
Number of digital inputs	16
Input current	
<ul style="list-style-type: none"> for signal "1", typ. 	3.7 mA
Standards, approvals, certificates	
Highest safety class achievable in safety mode	
<ul style="list-style-type: none"> Performance level according to ISO 13849-1 SIL acc. to IEC 61508 	e 3
Dimensions	
Width	90 mm
Height	130 mm
Depth	65 mm

last modified: 8/27/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6ES71484FA000AB0](#)