

SIMATIC DP, Connection module for PROFINET interface module, ET 200 PRO, connection 2xRJ45, 2x push-pull plug-in connectors for PROFINET PN



Figure similar

Input current	
from supply voltage 1L+, max.	No current consumption, only infeed current, max. 16 A with derating
from load voltage 2L+ (without load), max.	No current consumption, only infeed current, max. 16 A with derating
Accessories	
Function description	IM PN, 2x RJ45, 2x PushPull interface module
belongs to product	IM154-4 PN HF
Dimensions	
Width	90 mm
Height	130 mm
Depth	51 mm
Weights	
Weight, approx.	325 g

last modified: 8/16/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6ES71944AF000AA0](#)